

## Shelf trolley base module with wire grid, zinc-plated

With practical push handles


**fetra**  
Transportgeräte

### Execution:

- Modular system
- Profile steel/steel tube structure, completely bright galvanised
- Front walls made of steel tube with welded-in wire welding grid. Mesh size 100 x 50 mm, reinforced by 2 longitudinal struts
- Shelf in base frame with welded-in wire welding grid, mesh size 120 x 30 mm
- 2 tubular push handles with soft-grip on one side can be screwed on vertically
- 4 TPU (thermoplastic polyurethane) deflector rings on the castors
- optional shelves in 100 mm grid, can be hooked in horizontally or tilted

### Advantage:

- A multifunctional modular system with the fetra plug-in and screw principle. The picking trolleys can be changed, replaced and supplemented in many ways.
- Wide range of accessories



<b>Art. no.</b>	<b>50268 003</b>
<b>Brand</b>	FETRA
<b>Manufacturer Part Number</b>	28200
<b>Load-carrying capacity</b>	200 kg
<b>Loading surface length</b>	650 mm
<b>Loading-surface width</b>	510 mm
<b>Length</b>	891 mm
<b>Width</b>	590 mm
<b>Height</b>	1625 mm
<b>Loading surface size</b>	650 x 510 mm
<b>Loading-surface height</b>	193 mm
<b>Length x width x height</b>	891 x 590 x 1625 mm
<b>Wheel diameter</b>	125 mm
<b>Wheel width</b>	32 mm
<b>Material of wheel</b>	TPE
<b>Total stop optional</b>	No
<b>Gross Weight</b>	25.000 kg
<b>Product Group</b>	5AB

### EAN

4017976282008