

LED PIPE TOP ENTRY HIGH OUTPUT

LED PIPE G2 L1200 TOP ENTRY HIGH OUTPUT NW

0051056



Product features

- LED T5 replacement batten, with top entry cable, the power cables can be therefore hidden, high output range: more lumens per meter with efficiency up to 125 lum/watt, Ideal for direct lighting in kitchens, on wall or ceiling, 150 degree beam angle, includes switch, includes 0.30m stripped cable, white polycarbonate body, includes standard and tilting brackets



PRODUCT OVERVIEW

| | |
|---------------------------------|--|
| Product name | LED PIPE G2 L1200 TOP ENTRY HIGH OUTPUT NW |
| Technology | LED |
| Housing | PC Polycarbonate |
| General application | Residential & Consumer |
| ETIM Class | EC000109 |
| E-number FI | 4170548 |
| Warranty | 3 years |
| Fixture luminous flux (lm) | 2000 |
| Luminaire efficacy (lm/W) | 125 |
| Colour temperature (K) | 4000 |
| Light colour | Neutral White |
| CRI (Ra) | 80 |
| Colour Variation Initial (SDCM) | SDCM6 |
| Beam Angle (°) | 150 |
| Photobiological Risk Group | RG0 |
| Total power consumption (W) | 16 |
| Electrical protection | Class II |
| Dimmable | No |
| Housing colour | White |
| IP rating | IP20 |
| IK rating | IK02 |
| Product EAN number | 5410288510569 |

DATA TABLE

General data

| | |
|---|--|
| Product name | LED PIPE G2 L1200 TOP ENTRY HIGH OUTPUT NW |
| Technology | LED |
| Housing | PC Polycarbonate |
| General application | Residential & Consumer |
| Operating temperature range (°C) | -20°C...+40°C |
| Performance ambient temperature Tq (°C) | 25 |
| ETIM Class | EC000109 |

LED PIPE TOP ENTRY HIGH OUTPUT

LED PIPE G2 L1200 TOP ENTRY HIGH OUTPUT NW

0051056

| | |
|-------------|---------|
| E-number FI | 4170548 |
| Warranty | 3 years |

Optical data

| | |
|---------------------------------|---------------|
| Fixture luminous flux (lm) | 2000 |
| Luminaire efficacy (lm/W) | 125 |
| Colour temperature (K) | 4000 |
| Light colour | Neutral White |
| CRI (Ra) | 80 |
| Colour Variation Initial (SDCM) | SDCM6 |
| Beam Angle (°) | 150 |
| Photobiological Risk Group | RG0 |

Electrical data

| | |
|-----------------------------------|----------|
| Total power consumption (W) | 16 |
| Mains voltage (V) | 220-240V |
| Lamp power factor | 0.9 |
| Electrical protection | Class II |
| Dimmable | No |
| Drive current (mA) | 125 |
| Inrush Current (A) | 2 |
| Inrush Duration (µs) | 50 |
| Nominal Frequency (Hz) | 50/60Hz |
| Max. Luminaires per 10A C Breaker | 10 |
| Max. Luminaires per 13A C Breaker | 10 |
| Max. Luminaires per 16A C Breaker | 10 |
| Max. Luminaires per 20A C Breaker | 10 |
| Max. Luminaires per 10A B Breaker | 10 |
| Max. Luminaires per 13A B Breaker | 10 |
| Max. Luminaires per 16A B Breaker | 10 |
| Max. Luminaires per 20A B Breaker | 10 |

Lifetime data

| | |
|------------------|-------|
| Lifespan L70 B50 | 30000 |
|------------------|-------|

Physical data

| | |
|-----------------------------|------------------|
| Housing colour | White |
| IP rating | IP20 |
| IK rating | IK02 |
| Diffuser material | PC Polycarbonate |
| Nominal Product Length (mm) | 1200 |
| Nominal Product Width (mm) | 24 |
| Nominal Product Height (mm) | 35 |
| Weight (kg) | 0.222 |

Packaging

| | |
|---------------------------------------|---------------|
| Single packaging type | Carton |
| Product EAN number | 5410288510569 |
| Packaging single length / height (cm) | 5.0 |


LED PIPE TOP ENTRY HIGH OUTPUT LED PIPE G2 L1200 TOP ENTRY HIGH OUTPUT NW 0051056

| | |
|--------------------------------------|----------------|
| Packaging single width (cm) | 3.2 |
| Packaging single depth (cm) | 131.0 |
| DUN14 (outer) | 15410288510566 |
| Units per outer package | 20 |
| Packaging outer length / height (cm) | 133.0 |
| Packaging outer width (cm) | 22.0 |
| Packaging outer depth (cm) | 19.0 |

Safety data

| | |
|----------------------------------|--------|
| Optimal operating condition (°C) | -20-40 |
|----------------------------------|--------|

PHOTOMETRY



TECHNICAL DRAWINGS

