

Miniature cutting insert, type AF HC5640 for axial recessing

ATORN[®]

Application

For axial recessing in the material groups of steel and (stainless steel) with low to high cutting speeds and medium cutting conditions.

Version

- solid carbide cutting insert with inner cooling

Advantage

- tough cemented carbide type for broad application field
- sturdy geometry for axial cutter insert
- ideal for use with inefficient machines and unstable cutting conditions



Art. No.	17132 136
ISO name	AF
Shaft diameter	6 mm
Length	51 mm
Clearance length	22 mm
Recessing width	2 mm
Plunge depth	3 mm
Programming size	2.75 mm
Min. bore diameter	8 mm
Machining direction	Left
Carbide type	HC5640
Material to be processed	Steel, Stainless steel, Non-ferrous metal, Cast metal

EAN-Code

4050293267228