

# SP60/24

Solid Parabola, 600 mm, 21 dBi




## Specifications

Type	solid parabola 600 mm
Polarization	linear, mounting in steps of 45°
Frequency	2400-2485 MHz
Impedance	50 ohm
VSWR	≤1.7:1
Gain	21 dBi
HPBW	13° (E- and H-plane)
F/B	>25 dB
Cross polarization	>25 dB
Connector	N female
Power handling	20 W
Diameter	610 mm
Depth	150 mm excl mounting bracket 250 mm incl mounting bracket
Weight	2,7 kg incl mounting bracket
Material	reflector - 2 mm aluminium mount - aluminium, galvanized steel feeder - stainless steel
Color	white
Other	DC grounded


## Product No

28321

Smarteq reserves the right to change specifications without prior notice.



E-field radiation pattern, ie elevation for vertically polarised antenna.



H-field radiation pattern, ie azimuth for vertically polarised antenna.

**SMARTEQ™**  
■■■■■ antennas

**Smarteq Wireless AB**

P.O. Box 4064 | SE-182 04 Enebyberg | Sweden

[www.smarteq.com](http://www.smarteq.com)



Smarteq is certified according to  
ISO/TS 16949, ISO 14001

550042C

Smarteq develops and supplies high-quality antennas and antenna systems for the wireless transfer of speech and data, communication to and from vehicles and machine to machine. Our staff is fully focused on developing high-performance antennas that will continue to set new standards of excellence that will exceed our customers' expectations