

MVVN clamp holder, negative, neutral

For copy and longitudinal turning with VN indexable insert

ATORN[®]

Application


For copy and longitudinal turning with VN indexable insert, 35°.

Version

- Precision-manufactured steel support, burnished, hardened, adjustable clamping system, type V, working angle 93°, tip angle 35°, clearance angle 0°

Advantage

- Very streamlined geometry, optimised for contour lathe work with large feed depths and unfavourable conditions
- Negative geometry of the body ensures good stability and force absorption at large cutting depths
- Broad range of use: suitable for both finishing and roughing operations
- Adjustable clamp minimises vibrations and ensures good force transfer



Art. No.	17859 200
ISO name	MVVN N 2020 K16
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Programming size	10.0 mm
Length of head	43 mm
Suitable for indexable inserts	VN.. 1604..
Tool design	Neutral
DIN	4983

EAN-Code

4050293127782