



Part no.: 50112142
TK BR 53
Reflector

Figure can vary

Contents

- Technical data
- Dimensioned drawings

Part no.: 50112142 – TK BR 53 – Reflector

Technical data

Basic data

Area of application Food

Mechanical data

Design	Rectangular
Mounting dimension, width	14 mm
Reflection surface width	29 mm
Mounting dimension, height	36 mm
Reflection surface height	10 mm
Mounting dimension, thickness	20.3 mm
Triple reflector size	0.3 mm
Reflector material	Plastic
Material of base material	Stainless steel
Chemical designation, reflector material	Stainless steel
Structure, active surface	Mikrotriple
Net weight	50 g
Type of fastening	Housing fit

Environmental data

Ambient temperature, operation -30 ... 70 °C

Certifications

Degree of protection IP 67
IP 69K

Classification

Customs tariff number	73269098
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

Dimensioned drawings

All dimensions in millimeters

Part no.: 50112142 – TK BR 53 – Reflector

