IEC Plug E, Cord Connector (Rewireable), Straight, max. Cable Diameter 10 mm





Rewireable connector

Example with assembled cable



70° C

See below:

Approvals and Compliances

Description

- Cord Connectors (Rewireable): Screw-on mounting
- 1 Function
- Appliance Inlet , Pin temperature 70 $^{\circ}\text{C}$, Protection class I
- Cable

Weblinks

pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Accessories, Detailed request for product

Technical Data

10A / 250VAC; 50Hz
15 A / 250 VAC; 60 Hz
> 2 kVAC between L-N > 2 kVAC between L/N-PE (1 min/50 Hz)
-25°C to 70°C
Suitable for appliances with protection class I acc. to IEC 61140
Cable
Thermoplastic, black, UL 94V-0

Appliance inlet/-outlet	E acc. to IEC 60320-3,
	UL 498, CSA C22.2 no. 42 (for cold
	conditions) pin-temperature 70 °C, 10A,
	Protection Class I

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: 4735

Approval Logo	Certificates	Certification Body	Description
© ^V E	VDE Approvals	VDE	VDE Certificate Number: 40011482
c U_L U_S	UL Approvals	UL	UL File Number: E96454
(1)	CCC Approvals	CCC	CCC Certificate Number:

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
<u>IEC</u>	Designed according to	IEC 60320-3	Appliance couplers for household and similar general purposes
(UL)	Designed according to	UL 498	Standard for Attachment Plugs and Receptacles
GF CSA Group	Designed according to	CSA C22,2 no. 42	General Use Receptacles, Attachment Plugs, and Similar Wiring Devices

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
<u>IEC</u>	Designed for applications acc.	IEC/UL 62368-1	IEC 62368-1 includes the basic requirements for safety of audio, video, information technology and office equipment.


Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
ROHS COMPLANT	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
50)	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimensions [mm]

4735



All Variants

Color	Recommended cable diameter	Max, wire size	L = Length of cable guard	Order Number	
black	10 mm	3 x 1.5 mm² / 3 x 14 AWG	-	4735.0000	

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Max. torque for screws: Terminals: 0.5 Nm, Cable clamps: 0.3 Nm, Cover: 0.3 Nm

Packaging unit 100 Pcs

Accessories

Description



Cord retaining kits Cord retaining strain relief

Countersunk, F	4700.0006
Flat head, G	4700.0007

Mating Outlets/Connectors

Category / Description

Appliance Outlet Overview complete



6600-5, Mounting: Snap-in version, Appliance Outlet: IEC F, For PCB mounting, 10 A, Suitable for appliances with 6600-5 protection class I $6600\hbox{--}3, Mounting: Screw-on mounting, Appliance \ Outlet: IEC\ F, Solder/Quick\ Connect\ Terminal,\ 10\ A,\ Suitable\ for$ 6600-3 appliances with protection class I 4787, Mounting: Screw-on mounting, Appliance Outlet: IEC Solder terminals, 10 A, Suitable for appliances with pro-4787 4788, Mounting: Snap-in version, Appliance Outlet: IEC Solder/Quick Connect Terminal, 10 A, Suitable for appliances 4788 with protection class I 6600-4, Mounting: Snap-in version, Appliance Outlet: IEC F, Solder/Quick Connect Terminal, 10 A, Suitable for appli-6600-4

Appliance Outlet shuttered Overview complete



4721, Mounting: Screw-on mounting, Appliance Outlet: IEC F, Solder/Quick Connect Terminal, 10 A, Suitable for appli-4721 ances with protection class I 4723, Mounting: Snap-in version, Appliance Outlet: IEC F, Solder/Quick Connect Terminal, 10 A, Suitable for appliances with protection class I

Connector Overview complete

ances with protection class I



4782 Mounting: Power Cord, 3 x 1 mm² / 3 x 18 AWG, Cable, Connector: IEC C13 4782 4785 Mounting: Power Cord, 3 x 1 mm² / 3 x 18 AWG, Cable, Connector: IEC C13 4785 4300-06 Mounting: Power Cord, 3 x 1 $\,mm^2$ / 3 x 18 AWG, Cable, Connector: IEC C13 4300-06 4781 4781 Mounting: Power Cord, Cable, Connector: IEC C15 4784 Mounting: Power Cord, 3 x 1 mm 2 / 3 x 18 AWG, Cable, Connector: IEC C15 4784

Distribution Unit Overview complete



4751 , Mounting: Snap-in, Front Side, Solder pin or quick connect terminals 6.3×0.8 or 4.8×0.8 mm, x Appliance Outlet: IEC F	4751
0712-PQ, Mounting: Snap-in, Front Side, Solder terminal (4.8 x 0.8 mm), 1x Appliance Outlet: IEC F	0712
4741, Mounting: 2x Appliance Outlet: IEC F	4741
0909, Mounting: Snap-in, Front Side, Solder terminals, 7x Appliance Outlet: IEC F	0909
4752, Mounting: Snap-in, Front Side, Solder/Quick Connect Terminal, 4x Appliance Outlet: IEC F	4752

Category / Description

Power Entry Module Overview complete



IEC Appliance Inlet C14 with Appliance Outlet F	KP (Outlet)
Felcom 64, Mounting: 0 mm, Fuseholder: Solder terminals 3.5 x 0.8 mm or quick connect terminals 6.3 x 0.8 mm, Rocker switch: 2-pole non-illuminated, Appliance Inlet: IEC C14, Power Entry Module	Felcom 64
4719, Mounting: Snap-in, mm, Fuseholder: 1-pole, Appliance Outlet: IEC F, with or without neon indicator, Suitable for appliances with protection class I	4719



Power Entry Module with line filter Overview complete

Felcom 54, Mounting: mm, Front Side, Filter: Standard version, Fuseholder: 1-/2-pole, Front Side, 10 A, Rocker switch: 2-pole, Solder terminals 3.5×0.8 mm or quick connect terminals 6.3×0.8 mm, Appliance Inlet: IEC C14 Felcom 54