


## 1633A Multi-Conductor - Category 5 Nonbonded-Pair ScTP Cable



For more Information  
please call

1-800-Belden1



### General Description:

CAT5, 4-Pair, U/UTP-Unshielded, CM Rated, Premise Horizontal Cable, 24 AWG solid bare copper conductors, Polyolefin insulation, overall Beldfoil® Shield, Ripcord, PVC jacket

### Usage (Overall)

Suitable Applications: Premise Horizontal Cable

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

Total Number of Conductors: 8

#### Insulation

##### Insulation Material:

Insulation Material
PO - Polyolefin

#### Outer Shield

##### Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

##### Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	Solid	TC - Tinned Copper

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

##### Outer Jacket Diameter:

Nom. Dia. (in.)
0.260

Outer Jacket Ripcord: Yes

#### Pair

##### Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

### Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

Bulk Cable Weight: 28 lbs/1000 ft.

Max. Recommended Pulling Tension: 25 lbs.

Min. Bend Radius/Minor Axis: 1 in.

Min. Bend/Installation: 2.600 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CM, UL444

CEC/(UL) Specification: CM

## 1633A Multi-Conductor - Category 5 Nonbonded-Pair ScTP Cable

EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	568 TSB 36, Category 5
Other Specification:	UL verified to TSB 36, Category 5

### Flame Test

UL Flame Test:	UL1685 UL Loading
CSA Flame Test:	FT1

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Electrical Characteristics (Overall)

#### Nom. Mutual Capacitance:

Capacitance (pF/ft)  
15

Maximum Capacitance Unbalance (pF/100 m): 330

#### Nominal Velocity of Propagation:

VP (%)  
67

#### Maximum Delay:

Delay (ns/100 m)  
538 @ 100MHz

#### Max. Delay Skew:

Delay Skew (ns/100 m)  
45

#### Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)  
9.38

#### Max. Operating Voltage - UL:

Voltage  
300 V RMS

#### Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)  
5

### Electrical Characteristics-Premise (Overall)

#### Premise Cable Electricals:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. SRL (dB)	Fitted Imp. (Ohms)
1	2.0	62.3	No Spec	No Spec	100 ± 15%
4	4.1	53.3	No Spec	No Spec	100 ± 15%
8	5.8	48.8	No Spec	No Spec	100 ± 15%
10	6.5	47.3	No Spec	No Spec	100 ± 15%
16	8.2	44.3	No Spec	No Spec	100 ± 15%
20	9.3	42.8	No Spec	No Spec	100 ± 15%
25	10.4	41.3	No Spec	No Spec	100 ± 15%
31.25	11.7	39.9	No Spec	No Spec	100 ± 15%
62.5	17.0	35.4	No Spec	No Spec	100 ± 15%
100	22.0	32.3	No Spec	No Spec	100 ± 15%

### Notes (Overall)

Notes: Not compatible with RJ-11/12/45 telephone plugs. Jacket sequentially marked at 2 ft. intervals. Third party verified to TIA/EIA-568-TSB 36, Category 5.

### Put Ups and Colors:

## 1633A Multi-Conductor - Category 5 Nonbonded-Pair ScTP Cable

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 1    Revision Date: 02-06-2013

© 2017 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).