


Stainless Steel Low Profile Vandal Resistant - Momentary


FRONT PANEL MOUNTING MP0027

- 28mm diameter
- S.P.C.O. Microswitch
- 5A, 250Vac




MP0038 Sealed to IP66

- Front Panel Sealed to IP66
- 28mm diameter
- S.P.C.O. Microswitch
- 5A, 250Vac





- 22mm diameter
- S.P.C.O. Microswitch
- 5A, 250Vac




Specification	MP0027	MP0038	MP0025
Terminations:	Solder Tags	Solder Tags	Solder Tags
Switching:	S.P.C.O. Momentary Action (Microswitch)	S.P.C.O. Momentary Action (Microswitch)	S.P.C.O. Momentary Action (Microswitch)
Max. Rating:	5A, 250Vac 2A, 28Vdc	5A, 250Vac 2A, 28Vdc	5A, 250Vac 2A, 28Vdc
Contact Resistance:	<10mΩ	<10mΩ	<10mΩ
Insulation Resistance:	$>10^3 M\Omega$	$> 10^3 M\Omega$.	$> 10^3 M\Omega$
Dielectric Strength:	>2.0kVac	>2.0kVac	>2.0kVac
Operating Temp. Range:	-20°C to +70°C	-20°C to +70°C	-20°C to +70°C
Sealing (Front of panel only):		Protection Classification: IP66 EN60529 1992 (Micro switch not sealed)	
Operations Mechanical: Electrical:	1,000,000 (min) 35,000 (min)	1,000,000 (min) 35,000 (min)	1,000,000 (min) 35,000 (min)
Operating Pressure:	7.5N (typ)	12.5N (typ)	6.1N (typ)
Rear Nut Fixing Torque:	2.5Nm	1.13Nm	-
Materials Mouldings: Tags/Terminations: Switch Body & Button:	Glass Filled Nylon Brass, Tin Plated Stainless Steel	Glass Filled Nylon Brass, Tin Plated Stainless Steel	Glass Filled Nylon Brass, Tin Plated Stainless Steel
Contacts:	Fine Silver	Fine Silver	Fine Silver
Thread size:	1.0" x 26TPI	1.0" x 26TPI	-
RoHS	Compliant	Compliant	Compliant



Stainless Steel Low Profile Vandal Resistant - Momentary


FRONT PANEL MOUNTING MP0037 Sealed to IP68

- Front Panel Sealed to IP68
- 21.5mm diameter
- S.P. Push to Make
- 1A, 50Vac/dc
- Industry Standard Size






- Front Panel Sealed to IP66
- 21.5mm diameter
- S.P.C.O. Microswitch
- 5A, 250Vac





- Rear Panel Mounting
- Flush with Panel
- 19mm diameter
- S.PC.O. Microswitch
- 5A, 250Vac



Specification	MP0037	MP0031	MP0034
Terminations:	Screw Terminals	Solder Tags	Solder Tags
Switching:	S.P. Push to make Momentary action	S.P.C.O. Momentary Action (Microswitch)	S.P.C.O. Momentary Action (Microswitch)
Max. Rating:	1A, 50Vac/dc	5A, 250Vac 2A, 28Vdc	5A, 250Vac 2A, 28Vdc
Contact Resistance:	<10mΩ	<10 m Ω	<10mΩ
Insulation Resistance:	$>10^5 M\Omega$	$>10^3 M\Omega$.	$> 10^3 M\Omega$
Dielectric Strength:	>1.0kVac	>2.0kVac	>2.0kVac
Operating Temp. Range:	-20°C to +70°C	-20°C to +70°C	-20°C to +70°C
Sealing (Front of panel only):	Protection Classification: IP68 EN60529 1992 (Terminals not sealed)	Protection Classification: IP66 EN60529 1992 (Micro switch not sealed)	
Operations Mechanical: Electrical:	1,000,000 (min) 30,000 (min)	1,000,000 (min) 35,000 (min)	250,000 (min) 35,000 (min)
Operating Pressure:	7.5N (typ)	4.7N (typ)	2.7N (typ)
Rear Nut Fixing Torque:	0.57Nm	0.57Nm	-
Materials Mouldings: Tags/Terminations: Switch Body & Button:	Glass Filled Nylon Brass, Silver Plated Stainless Steel	Glass Filled Nylon Brass, Tin Plated Stainless Steel	Glass Filled Nylon Brass, Tin Plated Stainless Steel
Contacts:	Brass, Silver Plated, Silver	Fine Silver	Fine Silver
Thread size:	0.747" x 26TPI	0.747" x 26TPI	-
RoHS	Compliant	Compliant	Compliant

www.elektron-bulgin.com 175