

Sample &

Buv





SCES204O - APRIL 1999-REVISED JANUARY 2015

# SN74LVC2G125 Dual Bus Buffer Gate With 3-State Outputs

Technical

Documents

#### 1 Features

- Available in the Texas Instruments NanoFree<sup>™</sup> Package
- Supports 5-V V<sub>CC</sub> Operation
- Inputs Accept Voltages to 5.5 V
- Max t<sub>pd</sub> of 4.3 ns at 3.3 V
- Low Power Consumption, 10-µA Max I<sub>CC</sub>
- ±24-mA Output Drive at 3.3 V
- Typical V<sub>OLP</sub> (Output Ground Bounce) < 0.8 V at V<sub>CC</sub> = 3.3 V,  $T_A = 25^{\circ}C$
- Typical V<sub>OHV</sub> (Output V<sub>OH</sub> Undershoot) > 2 V at V<sub>CC</sub> = 3.3 V, T<sub>A</sub> = 25°C
- I<sub>off</sub> Supports Live Insertion, Partial-Power-Down Mode, and Back-Drive Protection
- Can Be Used as a Down Translator to Translate Inputs From a Max of 5.5 V Down to the V<sub>CC</sub> Level
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model
  - 200-V Machine Model
  - 1000-V Charged-Device Model

# 2 Applications

- Cable Modem Termination Systems
- High-Speed Data Acquisition and Generation
- Military: Radars and Sonars
- Motor Controls: High-Voltage
- Power Line Communication Modems
- SSDs: Internal or External
- Video Broadcasting and Infrastructure: Scalable Platforms
- Video Broadcasting: IP-Based Multi-Format Transcoders
- Video Communications Systems

## 3 Description

Tools &

Software

The SN74LVC2G125 device is a dual bus buffer gate, designed for 1.65-V to 5.5-V V<sub>CC</sub> operation. This device features dual line drivers with 3-state outputs. The outputs <u>are</u> disabled when the associated output-enable ( $\overline{OE}$ ) input is high.

Support &

Community

20

NanoFree<sup>™</sup> package technology is a major breakthrough in IC packaging concepts, using the die as the package.


To ensure the high-impedance state during power up or power down, OE should be tied to  $V_{CC}$  through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

This device is fully specified for partial-power-down applications using  $I_{off}$ . The  $I_{off}$  circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.

PART NUMBER	PACKAGE	BODY SIZE
	SM8 (8)	2.95 mm × 2.80 mm
SN74LVC2G125	US8 (8)	2.30 mm × 2.00 mm
	DSBGA (8)	1.91 mm × 0.91 mm

(1) For all available packages, see the orderable addendum at the end of the data sheet.

# 4 Simplified Schematic



# **Table of Contents**

1		tures 1							
2	Арр	lications1							
3	Description 1								
4	Sim	plified Schematic1							
5	Rev	ision History 2							
6	Pin	Configuration and Functions 3							
7	Spe	cifications							
	7.1								
	7.2	ESD Ratings 4							
	7.3	Recommended Operating Conditions5							
	7.4	Thermal Information 5							
	7.5	Electrical Characteristics 6							
	7.6	Switching Characteristics 6							
	7.7	Switching Characteristics 6							
	7.8	Operating Characteristics7							
	7.9	Typical Characteristics 7							
8	Para	ameter Measurement Information							

# 5 Revision History

С	Changes from Revision N (November 2013) to Revision O	Page
•	Added Applications, Device Information table, Pin Functions table, ESD Ratings table, Thermal Information table, Typical Characteristics, Feature Description section, Device Functional Modes, Application and Implementation section, Power Supply Recommendations section, Layout section, Device and Documentation Support section, and Mechanical, Packaging, and Orderable Information section.	1
С		
	Changes from Revision M (January 2007) to Revision N	Page
٠		
•	Updated document to new TI data sheet format.	1
	Updated document to new TI data sheet format Removed Ordering Information table.	1

Added ESD warning. 12

9	Deta	iled Description	9
	9.1	Overview	9
	9.2	Functional Block Diagram	9
	9.3	Feature Description	9
	9.4	Device Functional Modes	9
10	Арр	lication and Implementation	10
	10.1	Application Information	10
	10.2	Typical Application	
11	Pow	ver Supply Recommendations	11
12	Lay	out	11
	12.1	Layout Guidelines	11
	12.2	Layout Example	11
13	Dev	ice and Documentation Support	12
	13.1	Trademarks	12
	13.2	Electrostatic Discharge Caution	12
	13.3	Glossary	12
14		hanical, Packaging, and Orderable mation	12




www.ti.com

#### 2



#### SN74LVC2G125 SCES2040 – APRIL 1999 – REVISED JANUARY 2015

## 6 Pin Configuration and Functions



See mechanical drawings for dimensions.

YZP PACKAGE (BOTTOM VIEW)					
GND	O4 50	2A			
2Y	O36O	1Y			
1A	0270	20E			
10E	0180	V <sub>cc</sub>			

See mechanical drawings for dimensions.

#### **Pin Functions**

P	IN						
NAME	DCT, DCU, YZP	TYPE	DESCRIPTION				
1A	2	I	Input				
2A	5	I	Input				
1 <mark>OE</mark>	1	I	ut Enable for buffer 1				
2 <del>0E</del>	7	I	ut Enable for buffer 2				
1Y	6	0	Output				
2Y	3	0	Output				
GND	4	—	Ground				
V <sub>CC</sub>	8	_	Power pin				



## 7 Specifications

## 7.1 Absolute Maximum Ratings

See<sup>(1)</sup>

			MIN	MAX	UNIT
$V_{CC}$	Supply voltage range	-0.5	6.5	V	
VI	Input voltage range <sup>(2)</sup>	-0.5	6.5	V	
Vo	Vo Voltage range applied to any output in the high-impedance or power-off state <sup>(2)</sup>				V
Vo	V <sub>O</sub> Voltage range applied to any output in the high or low state <sup>(2)(3)</sup>				V
I <sub>IK</sub>	Input clamp current	V <sub>1</sub> < 0		-50	mA
I <sub>OK</sub>	Output clamp current	V <sub>O</sub> < 0		-50	mA
I <sub>O</sub>	Continuous output current			±50	mA
	Continuous current through V <sub>CC</sub> or GND				mA
T <sub>stg</sub>	Storage temperature range		-65	150	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The input negative-voltage and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

(3) The value of  $V_{CC}$  is provided in the *Recommended Operating Conditions* table.

## 7.2 ESD Ratings

	PARAMETER DEFINITION		VALUE	UNIT
	Electrostatic	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins <sup>(1)</sup>	2000	
V <sub>(ESD)</sub>	discharge	Charged device model (CDM), per JEDEC specification JESD22-C101, all $pins^{(2)}$	1000	V

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



#### 7.3 Recommended Operating Conditions

over recommended operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

			MIN	MAX	UNIT	
V	Over the welter re-	Operating	1.65	5.5	N/	
V <sub>CC</sub>	Supply voltage	Data retention only	1.5		V	
		V <sub>CC</sub> = 1.65 V to 1.95 V	0.65 × V <sub>CC</sub>			
		$V_{CC}$ = 2.3 V to 2.7 V	1.7		V	
VIH	High-level input voltage	$V_{CC} = 3 V \text{ to } 3.6 V$	2		V	
		$V_{CC}$ = 4.5 V to 5.5 V	$0.7 \times V_{CC}$			
		V <sub>CC</sub> = 1.65 V to 1.95 V		$0.35 \times V_{CC}$		
	Low-level input voltage	$V_{CC}$ = 2.3 V to 2.7 V		0.7	V	
V <sub>IL</sub>		$V_{CC} = 3 V \text{ to } 3.6 V$		0.8	V	
		$V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$		$0.3 \times V_{CC}$		
VI	Input voltage	· · · · ·	0	5.5	V	
Vo	Output voltage	High or low state	0	V <sub>CC</sub>	V	
		3-state	0	5.5	V	
		V <sub>CC</sub> = 1.65 V		-4		
	High-level output current	$V_{CC} = 2.3 V$		-8		
I <sub>OH</sub>				-16	mA	
		V <sub>CC</sub> = 3 V		-24		
		V <sub>CC</sub> = 4.5 V		-32		
		V <sub>CC</sub> = 1.65 V		4		
		V <sub>CC</sub> = 2.3 V		8		
I <sub>OL</sub>	Low-level output current	N/ 0.1/		16	mA	
		$V_{CC} = 3 V$		24		
		$V_{CC} = 4.5 V$		32		
		$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}, 2.5 \text{ V} \pm 0.2 \text{ V}$		20		
Δt/Δv	Input transition rise or fall rate	$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$		ns/V		
		$V_{CC} = 5 V \pm 0.5 V$		<u> </u>		
T <sub>A</sub>	Operating free-air temperature		-40	125	°C	

 All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

## 7.4 Thermal Information

	DCT      DCU      YZP        8 PINS      8 PINS      8 PINS      8 PINS				
	8 PINS	8 PINS	8 PINS	UNIT	
R <sub>0JA</sub> Junction-to-ambient thermal resistance	220	227	102	°C/W	

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.

#### SN74LVC2G125

SCES204O - APRIL 1999-REVISED JANUARY 2015

www.ti.com

STRUMENTS

EXAS

#### 7.5 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

	TEST CONDITIONS		–40°0	C to 85°C	-40°C to 125°C			
PARAMETER		V <sub>cc</sub>	MIN	TYP <sup>(1)</sup> MAX	MIN	TYP <sup>(1)</sup>	MAX	UNIT
	I <sub>OH</sub> = -100 μA	1.65 V to 5.5 V	V <sub>CC</sub> – 0.1		V <sub>CC</sub> – 0.1			
	$I_{OH} = -4 \text{ mA}$	1.65 V	1.2		1.2			
	$I_{OH} = -8 \text{ mA}$	2.3 V	1.9		1.9			V
V <sub>OH</sub>	I <sub>OH</sub> = -16 mA	2.1/	2.4		2.4			
	$I_{OH} = -24 \text{ mA}$	3 V	2.3		2.3			
	I <sub>OH</sub> = -32 mA	4.5 V	3.8		3.8			
	I <sub>OL</sub> = 100 μA	1.65 V to 5.5 V		0.1			0.1	V
	I <sub>OL</sub> = 4 mA	1.65 V		0.45			0.45	
M	I <sub>OL</sub> = 8 mA	2.3 V		0.3			0.3	
V <sub>OL</sub>	I <sub>OL</sub> = 16 mA	- 3 V		0.4			0.4	
	I <sub>OL</sub> = 24 mA			0.55			0.55	
	I <sub>OL</sub> = 32 mA	4.5 V		0.55			0.75	
I <sub>I</sub> A or OE inputs	V <sub>I</sub> = 5.5 V or GND	0 to 5.5 V		±5			±5	μΑ
I <sub>off</sub>	$V_1 \text{ or } V_0 = 5.5 \text{ V}$	0		±10			±10	μA
I <sub>OZ</sub>	V <sub>O</sub> = 0 to 5.5 V	3.6 V		10			10	μΑ
I <sub>CC</sub>	$V_1 = 5.5 \text{ V or GND}, \qquad I_0 = 0$	1.65 V to 5.5 V		10			10	μΑ
ΔI <sub>CC</sub>	One input at $V_{CC} - 0.6 V$ , Other inputs at $V_{CC}$ or GND	3 V to 5.5 V		500			500	μA
Data inputs		2.2.1/		3.5		3.5		~ [
C <sub>i</sub> Control inputs	$V_{I} = V_{CC}$ or GND	3.3 V		4		4		pF
Co	V <sub>O</sub> = V <sub>CC</sub> or GND	3.3 V		6.5		6.5		pF

(1) All typical values are at  $V_{CC} = 3.3$  V,  $T_A = 25^{\circ}C$ .

## 7.6 Switching Characteristics

over recommended operating free-air temperature range (unless otherwise noted) (see Figure 3)

						–40°C t	o 85°C				
PARAMETER FROM (INPUT)		TO (OUTPUT)		V <sub>CC</sub> = 1.8 V ± 0.15 V		V <sub>CC</sub> = 2.5 V ± 0.2 V		3.3 V V	V <sub>CC</sub> = 5 V ± 0.5 V		UNIT
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t <sub>pd</sub>	A	Y	3.3	9.1	1.5	4.8	1.4	4.3	1	3.7	ns
t <sub>en</sub>	ŌĒ	Y	4	9.9	1.9	5.6	1.2	4.7	1.2	3.8	ns
t <sub>dis</sub>	OE	Y	1.5	11.6	1	5.8	1.4	4.6	1	3.4	ns

## 7.7 Switching Characteristics

over recommended operating free-air temperature range (unless otherwise noted) (see Figure 3)

						-40°C to	o 125°C				
PARAMETER	FROM (INPUT)	TO (OUTPUT)	V <sub>CC</sub> = 7 ± 0.1		V <sub>CC</sub> = 2 ± 0.2		V <sub>CC</sub> = 3 ± 0.3		V <sub>CC</sub> = ± 0.5		UNIT
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t <sub>pd</sub>	А	Y	3.3	10.1	1.5	5.8	1.4	5.3	1	4.2	ns
t <sub>en</sub>	OE	Y	4	10.9	1.9	6.6	1.2	5.7	1.2	4.3	ns
t <sub>dis</sub>	OE	Y	1.5	12.6	1	6.8	1.4	5.6	1	3.9	ns




# 7.8 Operating Characteristics


T <sub>A</sub> =	= 25°
------------------	-------

PARAMETER			TEST CONDITIONS	V <sub>CC</sub> = 1.8 V TYP	V <sub>CC</sub> = 2.5 V TYP	V <sub>CC</sub> = 3.3 V TYP	V <sub>CC</sub> = 5 V TYP	UNIT
0	Power dissipation	Outputs enabled	f 10 MU	19	19	20	22	~ <b>F</b>
C <sub>pd</sub>	C <sub>pd</sub> capacitance	Outputs disabled	f = 10 MHz	2	2	2	3	pF

## 7.9 Typical Characteristics





## 8 Parameter Measurement Information




TEST	S1
$t_{PLH}/t_{PHL}$	Open
$t_{PLZ}/t_{PZL}$	V <sub>load</sub>
$t_{PHZ}/t_{PZH}$	GND


	INF	PUTS				_		
V <sub>cc</sub>	V	t,/t,	V <sub>M</sub>	VLOAD	C	R	V	
1.8 V ± 0.15 V	V <sub>cc</sub>	≤2 ns	V <sub>cc</sub> /2	2 × V <sub>cc</sub>	30 pF	<b>1 k</b> Ω	0.15 V	
$2.5~V\pm0.2~V$	$V_{cc}$	≤2 ns	V <sub>cc</sub> /2	2 × V <sub>cc</sub>	30 pF	<b>500</b> Ω	0.15 V	
$3.3~V\pm0.3~V$	3 V	≤2.5 ns	1.5 V	6 V	50 pF	<b>500</b> Ω	0.3 V	
$5 V \pm 0.5 V$	$V_{cc}$	≤2.5 ns	V <sub>cc</sub> /2	2 × V <sub>cc</sub>	50 pF	<b>500</b> Ω	0.3 V	





INVERTING AND NONINVERTING OUTPUTS





NOTES: A. C<sub>L</sub> includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
  C. All input pulses are supplied by generators having the following characteristics: PRR ≤ 10 MHz, Z₀ = 50 Ω.
- D. The outputs are measured one at a time, with one transition per measurement.
- E.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
- F.  $t_{PZL}$  and  $t_{PHZ}$  are the same as  $t_{en}$ .
- G.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{en}$ .
- H. All parameters and waveforms are not applicable to all devices.

#### Figure 3. Load Circuit and Voltage Waveforms




## 9 Detailed Description

#### 9.1 Overview

The SN74LVC2G125 device contains dual buffer gate device with output enable control and performs the Boolean function Y = A. This device is fully specified for partial-power-down applications using  $I_{off}$ . The  $I_{off}$  circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down. To ensure the high-impedance state during power up or power down,  $\overline{OE}$  should be tied to  $V_{CC}$  through a pull-up resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

#### 9.2 Functional Block Diagram



#### 9.3 Feature Description

- Wide operating voltage range
  - Operates from 1.65 V to 5.5 V
- Allows down voltage translation
- Inputs accept voltages to 5.5 V
- I<sub>off</sub> Feature
  - Allows voltages on the inputs and outputs, when  $V_{CC}$  is 0 V

#### 9.4 Device Functional Modes

#### Table 1. Function Table

INPU	JTS	OUTPUT					
OE	Α	Y					
L	н	Н					
L	L	L					
Н	Х	Z					

TEXAS INSTRUMENTS

www.ti.com

#### **10** Application and Implementation

#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

#### **10.1** Application Information

The SN74LVC2G125 device is a high drive CMOS device that can be used as a output enabled buffer with a high output drive, such as an LED application. It can produce 24 mA of drive current at 3.3 V making it Ideal for driving multiple outputs and good for high speed applications up to 100 MHz. The inputs are 5.5-V tolerant allowing it to translate down to  $V_{CC}$ .

#### **10.2 Typical Application**




Figure 4. Typical Application Schematic

#### 10.2.1 Design Requirements

This device uses CMOS technology and has balanced output drive. Care should be taken to avoid bus contention because it can drive currents that would exceed maximum limits. The high drive will also create fast edges into light loads so routing and load conditions should be considered to prevent ringing.


#### 10.2.2 Detailed Design Procedure

- 1. Recommended Input Conditions:
  - For rise time and fall time specifications, see ( $\Delta t/\Delta V$ ) in the *Recommended Operating Conditions* table.
  - For specified high and low levels, see (V<sub>IH</sub> and V<sub>IL</sub>) in the *Recommended Operating Conditions* table.
  - Inputs are overvoltage tolerant allowing them to go as high as (V<sub>1</sub> max) in the *Recommended Operating Conditions* table at any valid V<sub>CC</sub>.
- 2. Recommend Output Conditions:
  - Load currents should not exceed (I<sub>O</sub> max) per output and should not exceed (Continuous current through V<sub>CC</sub> or GND) total current for the part. These limits are located in the *Absolute Maximum Ratings* table.
  - Outputs should not be pulled above V<sub>CC</sub>.



#### **Typical Application (continued)**

#### 10.2.3 Application Curves



## **11** Power Supply Recommendations

The power supply can be any voltage between the min and max supply voltage rating located in the *Recommended Operating Conditions* table.

Each V<sub>CC</sub> pin should have a good bypass capacitor to prevent power disturbance. For devices with a single supply a 0.1- $\mu$ F capacitor is recommended and if there are multiple V<sub>CC</sub> pins then a 0.01- $\mu$ F or 0.022- $\mu$ F capacitor is recommended for each power pin. It is ok to parallel multiple bypass caps to reject different frequencies of noise. 0.1- $\mu$ F and 1- $\mu$ F capacitors are commonly used in parallel. The bypass capacitor should be installed as close to the power pin as possible for best results.

## 12 Layout

#### 12.1 Layout Guidelines

When using multiple bit logic devices, inputs should not float. In many cases, functions or parts of functions of digital logic devices are unused. Some examples are when only two inputs of a triple-input AND gate are used, or when only 3 of the 4-buffer gates are used. Such input pins should not be left unconnected because the undefined voltages at the outside connections result in undefined operational states.

Specified in Figure 6 are rules that must be observed under all circumstances. All unused inputs of digital logic devices must be connected to a high or low bias to prevent them from floating. The logic level that should be applied to any particular unused input depends on the function of the device. Generally they will be tied to GND or  $V_{CC}$ , whichever makes more sense or is more convenient.

#### 12.2 Layout Example



Figure 6. Layout Diagram



## **13 Device and Documentation Support**

#### 13.1 Trademarks

NanoFree is a trademark of Texas Instruments. All other trademarks are the property of their respective owners.

#### 13.2 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

#### 13.3 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms and definitions.

## 14 Mechanical, Packaging, and Orderable Information

The following pages include mechanical packaging and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser based versions of this data sheet, refer to the left hand navigation.



13-Jun-2014

# PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
74LVC2G125DCTRE4	ACTIVE	SM8	DCT	8	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	C25 Z	Samples
74LVC2G125DCTRE6	ACTIVE	SM8	DCT	8	3000	Pb-Free (RoHS)	CU SNBI	Level-1-260C-UNLIM	-40 to 125	C25 Z	Samples
74LVC2G125DCTRG4	ACTIVE	SM8	DCT	8	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	C25 Z	Samples
74LVC2G125DCURE4	ACTIVE	US8	DCU	8	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	C25R	Samples
74LVC2G125DCURG4	ACTIVE	US8	DCU	8	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	C25R	Samples
74LVC2G125DCUTE4	ACTIVE	US8	DCU	8		TBD	Call TI	Call TI	-40 to 125		Samples
74LVC2G125DCUTG4	ACTIVE	US8	DCU	8	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	C25R	Samples
SN74LVC2G125DCTR	ACTIVE	SM8	DCT	8	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	C25 Z	Samples
SN74LVC2G125DCUR	ACTIVE	US8	DCU	8	3000	Green (RoHS & no Sb/Br)	CU NIPDAU   CU SN	Level-1-260C-UNLIM	-40 to 125	(25 ~ C25Q ~ C25R) CZ	Samples
SN74LVC2G125DCUT	ACTIVE	US8	DCU	8	250	Green (RoHS & no Sb/Br)	CU NIPDAU   CU SN	Level-1-260C-UNLIM	-40 to 125	(C25Q ~ C25R)	Samples
SN74LVC2G125YZPR	ACTIVE	DSBGA	YZP	8	3000	Green (RoHS & no Sb/Br)	SNAGCU	Level-1-260C-UNLIM	-40 to 125	(CM2 ~ CM7 ~ CMN)	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.



# PACKAGE OPTION ADDENDUM

13-Jun-2014

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF SN74LVC2G125 :

Automotive: SN74LVC2G125-Q1

NOTE: Qualified Version Definitions:

• Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

# PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

## TAPE AND REEL INFORMATION





# QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal										-		-
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
74LVC2G125DCURG4	US8	DCU	8	3000	180.0	8.4	2.25	3.35	1.05	4.0	8.0	Q3
74LVC2G125DCUTG4	US8	DCU	8	250	180.0	8.4	2.25	3.35	1.05	4.0	8.0	Q3
SN74LVC2G125DCUR	US8	DCU	8	3000	180.0	9.0	2.05	3.3	1.0	4.0	8.0	Q3
SN74LVC2G125YZPR	DSBGA	YZP	8	3000	178.0	9.2	1.02	2.02	0.63	4.0	8.0	Q1

TEXAS INSTRUMENTS

www.ti.com

# PACKAGE MATERIALS INFORMATION

18-Aug-2014



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
74LVC2G125DCURG4	US8	DCU	8	3000	202.0	201.0	28.0
74LVC2G125DCUTG4	US8	DCU	8	250	202.0	201.0	28.0
SN74LVC2G125DCUR	US8	DCU	8	3000	182.0	182.0	20.0
SN74LVC2G125YZPR	DSBGA	YZP	8	3000	220.0	220.0	35.0

# **MECHANICAL DATA**

MPDS049B - MAY 1999 - REVISED OCTOBER 2002

#### DCT (R-PDSO-G8)

PLASTIC SMALL-OUTLINE PACKAGE



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion

D. Falls within JEDEC MO-187 variation DA.



DCT (R-PDSO-G8) PLASTIC SMALL OUTLINE Example Board Layout Example Stencil Design (Note C,E) (Note D) - 6x0,65 - 6x0,65 8x0,25-8x1,55 3,40 3,40 Non Solder Mask Defined Pad Example Pad Geometry -0,30 (Note C) 1,60 Example -0,07 Non-solder Mask Opening All Around (Note E) 4212201/A 10/11

NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



DCU (R-PDSO-G8)

PLASTIC SMALL-OUTLINE PACKAGE (DIE DOWN)



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side.

D. Falls within JEDEC MO-187 variation CA.






- NOTES: A. All linear dimensions are in millimeters. В. This drawing is subject to change without notice.
  - C. Publication IPC-7351 is recommended for alternate designs.
  - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
  - E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



YZP (R-XBGA-N8)

DIE-SIZE BALL GRID ARRAY



- A. All linear dimensions are in millimeters. Dimension B. This drawing is subject to change without notice.
- C. NanoFree™ package configuration.

NanoFree is a trademark of Texas Instruments.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products		Applications	
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial
Interface	interface.ti.com	Medical	www.ti.com/medical
Logic	logic.ti.com	Security	www.ti.com/security
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com		
OMAP Applications Processors	www.ti.com/omap	TI E2E Community	e2e.ti.com
Wireless Connectivity	www.ti.com/wirelessconne	ctivity	

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2015, Texas Instruments Incorporated