

## Dot laser, green, 520 nm, 5 mW

DD520-5-3-F(16x65)-QCW-DOE  
Order Number: 70132564

Main Parameters (*)	min	typ	max	Unit
Wavelength	510	520	530	nm
Optical Output Power		5		mW
Operating Voltage	2.7	3	3.3	V DC
Operating Current	150	180	220	mA
Operating Temperature	-10		60	°C
Storage Temperature	-40		80	°C

### Main Data

Warranty 1 years

### Technical Parameters

Lifetime > 6,000 h  
RoHS yes

### Optical Parameters

Beam Shape	Dot
Laser Class	3R
Divergence	D - 0.5 mrad
Size of Laserdot	adjustable
Operating Distance	20 m
Optics	glass lens AR coated
Laser technology	Single Mode Diode
Stability	+/- 3% @ -10-50°C
Focus	adjustable
internal modulation frequency	1 kHz

### Electrical Parameters

Potential of Housing isolated  
Power Supply LFNT-3

### Mechanical Parameters

Size	Ø16x65 mm
Material	aluminium
Cable length	100 mm
Wire type	28AWG, Typ 1061, UL1061
Output Aperture	5 mm
Housing Color	black
Weight	24 g
PCB	no
Stripping of wire	5 mm

(\*) Over the complete operating temperature range

## Features



- For assembling with a 8mm DOE
- Low Power consumption
- Direct green laserdiode with 520nm
- Internal modulation


## Picture



## Cable color

Ground		black	GND
positive		red	2.7 - 3.3, typ 3 V DC

## Safety Label



## Valid Revision

| 28-APR-2020