www.vishay.com

VEMD2503X01, VEMD2523X01

Vishay Semiconductors

Silicon PIN Photodiode



DESCRIPTION

VEMD2503X01 and VEMD2523X01 are high speed and high sensitive PIN photodiodes in a miniature surface mount package (SMD) with dome lens. The clear epoxy allows light detection of a wide wavelength range from 350 nm to 1120 nm. The photo sensitive area of the chip is 0.23 mm².

FEATURES

- Package type: surface mount
- · Package form: GW, RGW
- Dimensions (L x W x H in mm): 2.3 x 2.3 x 2.55
- AEC-Q101 qualified
- High radiant sensitivity
- · Suitable for visible and neat infrared radiation
- Fast response times
- Angle of half sensitivity: $\varphi = \pm 35^{\circ}$
- · Package matched with IR emitter series VSMB2943X01
- Floor life: 4 weeks, MSL 2a, acc. J-STD-020
- · Lead (Pb)-free reflow soldering
- · Material categorization: For definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- · High speed photo detector
- Light curtain
- Detector for optical switch

PRODUCT SUMMARY			
COMPONENT	I _{ra} (μΑ)	φ (deg)	λ _{0.1} (nm)
VEMD2503X01	10	± 35	350 to 1120
VEMD2523X01	10	± 35	350 to 1120

Note

Test conditions see table "Basic Characteristics"

ORDERING INFORMATION				
ORDERING CODE	PACKAGING	REMARKS PACKAGE		
VEMD2503X01	Tape and reel	MOQ: 6000 pcs, 6000 pcs/reel	Reverse gullwing	
VEMD2523X01	Tape and reel	MOQ: 6000 pcs, 6000 pcs/reel	Gullwing	

Note

MOQ: minimum order quantity

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage		V _R	60	V
Power dissipation	$T_{amb} \le 25 \ ^{\circ}C$	Pv	215	mW
Junction temperature		Tj	100	°C
Operating temperature range		T _{amb}	- 40 to + 100	°C
Storage temperature range		T _{stg}	- 40 to + 100	°C
Soldering temperature	Acc. reflow solder profile fig. 7	T _{sd}	260	°C
Thermal resistance junction/ambient	Acc. J-STD-051	R _{thJA}	250	K/W

ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000





COMPLIANT

HALOGEN FREE GREEN (5-2008)



Vishay Semiconductors

BASIC CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Forward voltage	I _F = 50 mA	VF		1		V
Breakdown voltage	I _R = 100 μA, E = 0	V _(BR)	32			V
Reverse dark current	V _R = 10 V, E = 0	I _{ro}		1	10	nA
Diode capacitance	$V_{R} = 0 V, f = 1 MHz, E = 0$	CD		4		pF
	$V_{R} = 5 V, f = 1 MHz, E = 0$	CD		1.3		pF
Open circuit voltage	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	Vo		350		mV
Temperature coefficient of Vo	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	TK _{Vo}		- 2.6		mV/K
Short circuit current	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	I _k		10		μA
Temperature coefficient of I_k	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	ΤΚ _{lk}		0.1		%/K
Reverse light current	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$, $V_R = 5 \text{ V}$	I _{ra}	7	10	14	μA
Angle of half sensitivity		φ		± 35		deg
Wavelength of peak sensitivity		λρ		900		nm
Range of spectral bandwidth		λ _{0.1}		350 to 1120		nm
Rise time	$V_R = 10 \text{ V}, \text{R}_L = 1 \text{k}\Omega, \lambda = 820 \text{nm}$	t _r		100		ns
Fall time	$V_{B} = 10 V, R_{L} = 1 k\Omega, \lambda = 820 nm$	t _f		100		ns

BASIC CHARACTERISTICS (Tamb = 25 °C, unless otherwise specified)




Fig. 1 - Reverse Dark Current vs. Ambient Temperature




Fig. 2 - Relative Reverse Light Current vs. Ambient Temperature




Fig. 3 - Reverse Light Current vs. Irradiance




Fig. 4 - Diode Capacitance vs. Reverse Voltage

2 For technical questions, contact: <u>detectortechsupport@vishay.com</u> Document Number: 84163

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000








Fig. 5 - Relative Spectral Sensitivity vs. Wavelength

REFLOW SOLDER PROFILE





VEMD2503X01, VEMD2523X01

Vishay Semiconductors




Fig. 6 - Relative Radiant Intensity vs. Angular Displacement

DRYPACK

Devices are packed in moisture barrier bags (MBB) to prevent the products from moisture absorption during transportation and storage. Each bag contains a desiccant.

FLOOR LIFE

Floor life (time between soldering and removing from MBB) must not exceed the time indicated on MBB label: Floor life: 4 weeks Conditions: $T_{amb} < 30$ °C, RH < 60 % Moisture sensitivity level 2a, acc. to J-STD-020.

DRYING


In case of moisture absorption devices should be baked before soldering. Conditions see J-STD-020 or label. Devices taped on reel dry using recommended conditions 192 h at 40 °C (+ 5 °C), RH < 5 %.


For technical questions, contact: <u>detectortechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>


Vishay Semiconductors




PACKAGE DIMENSIONS in millimeters: VEMD2503














technical drawings according to DIN specifications

Dimensions in mm Not indicated tolerances ±0.2







Drawing refers to following types:

Drawing-No.: 6.544-5409.01-4

Issue: prel. 03.08.12

VSMB2943RGX01 VSMF2893RGX01 VEMD2x23X01

Rev. 1.0, 05-Apr-13

4

Document Number: 84163


For technical questions, contact: <u>detectortechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000


VEMD2503X01, VEMD2523X01




Vishay Semiconductors

PACKAGE DIMENSIONS in millimeters: VEMD2523












Dimensions in mm Not indicated tolerances ±0.2







Drawing refers to following types:


Drawing-No.: 6.544-5408.01-4 Issue: prel; 03.08.12 VSMB2943GX01 VSMF2893GX01 VEMD2x23X01

VEMD2503X01, VEMD2523X01

Vishay Semiconductors

TAPING AND REEL DIMENSIONS in millimeters: VEMD2503

www.vishay.com




Drawing refers to following types: Reel dimensions and tape see table

Drawing-No.: 9.800-5100.02-4 Issue: prel; 03.08.12



Vishay Semiconductors

TAPING AND REEL DIMENSIONS in millimeters: VEMD2523



Drawing refers to following types: see table Reel dimensions and tape Drawing-No.: 9.800-5091.21-4 Issue: prel; 03.08.12

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.