

## Between Series Adaptor 33\_N-SMA-50-1/113\_N

### Description

Adaptor plug/jack  
N plug (male) / SMA jack (female)

Interface standards  
Series N - IEC 61169-16\_MIL-STD-348A/304\_CECC 22210  
Series SMA - IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 18 GHz

#### Mechanical Data

Number of matings 500  
Weight 0.0299 kg

#### Environmental Data

Operating temperature -65 °C to 165 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Interface - N plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - SMA jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

### Related Documents

Outline drawing DOU-00014305

### Ordering Information

Single package 33\_N-SMA-50-1/113\_NE