

NEOMILL permanent magnet clamping plates

With continuous transverse pole pitch $P = 15 \text{ mm}$, with neodymium magnets, reinforced system.



Application:

Suitable for heavy and rough machining. The dense, maximum concentrated magnetic field allows applications for small, medium and large workpieces, even with rough or uneven surfaces.

Execution:

- With narrow transverse pole pitch.
- High-adhesion neodymium magnet system.
- The pole pitch allows universal clamping, even for workpieces with rough or uneven contact surfaces.
- Maximum stability due to single-piece housing and solid pole plate.
- ON/OFF switch via hand lever.
- In the OFF position, a weak opposing field facilitates the removal of workpieces.

Advantage:

- Double neodymium magnetic system for high adhesive force up to 150 N/cm^2 .
- Adhesive force from 6 mm workpiece thickness.
- Sealed against dirt and coolant.

Delivery:

1x permanent magnet clamping plate; incl. adjustable clamps, hex key and instructions.



Art. no.	24341 150
Brand	SAV WALKER HAGOU
Manufacturer Part Number	243.11-400X200-NM
Length of clamping surface	400 mm
Magnet width	200 mm
Magnetic field height	12 mm
Height	60 mm
Pole pitch ST/NE	12/3 mm
Pole plate thickness	23 mm
Wear of pole surface	5 mm
Weight	35 kg
Gross Weight	38.700 kg
Product Group	230