

BLS 2.5 E sheet metal shears



Execution:

- high performance and powerful motor when it comes to the most difficult tasks.
- quad reversible blade for clean and burr-free cuts with low operating costs.
- ideal for trimming and cutting.

Advantage:

- good curve-negotiating properties with low sheet metal deformation.
- unrestricted view of the cutting line, which allows faster work progress.

Delivery:

moving and stationary blade, 1 pair of wrenches, 1 steel deflector



Art. no.	70375 410
Brand	FEIN
Manufacturer Part Number	72303561000
Model	BLS 2.5 E
Manufacturer Article Number	72303561000
Max. cutting capacity in sheet metal (400 N/mm²)	2.5 mm
Max. cutting capacity in sheet metal (600N/mm²)	2 mm
Max. cutting capacity in sheet metal (800N/mm²)	1.6 mm
Max. cutting capacity in aluminium sheet (250 N/mm²)	3 mm
Min./max. cutting speed	3-6 m/min
Min. radius	20 mm
Power input	350 W
Power output	210 W
Cable length	5 m
Stroke rate	1700 rpm
Weight	2.1 kg
Gross Weight	3.509 kg
Product Group	704

EAN

4014586874944