# **Data Sheet**



# Within Series Adaptor 32\_716-50-0-5/133\_W

#### Description

PIM Adaptor plug/plug 7/16 plug (male) / 7/16 plug (male)

Interface standard

Series 7/16 - IEC 61169-4\_CECC 22190\_DIN 47223\_VG 95250

#### **Benefits**

Low passive intermodulation (PIM) adaptor

#### **Technical Data**



 $\begin{array}{ll} \text{Impedance} & 50 \ \Omega \\ \text{Interface frequency max.} & 7.5 \ \text{GHz} \end{array}$ 

PIM, 3rd order intermodulation distortion (IMD) max. Static -155 dBc at 2x 43 dBm / 20 W carrier

**Mechanical Data** 

Number of matings 500 Weight 0.129 kg

**Environmental Data** 

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102) -65 °C to 165 °C compliant

#### **Material Data**

Interface - 7/16 plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating

## Interface - 7/16 plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating

#### **Related Documents**

Outline drawing DOU-00287212

### **Ordering Information**

Single package 32\_716-50-0-5/133\_WE

#### Remarks

PIM typ. -160 dBc at 2 x 20 W / 43 dBm

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.