

Pneumatic thread cutter GE 8-500 P

**MANNESMANN
DEMAG**

Execution:

- Ergonomic aluminium handle
- Reversible forward and reverse travel with rocker arm
- Cutting into steel up to 6 mm
- Cutting into light metal up to 8 mm

Advantage:

- Quiet and powerful
- Floating chuck allows easy cutting

Delivery:

Floating chuck



Art. no.	75061 420
Brand	MANNESMANN DEMAG
Manufacturer Part Number	47060065
Model	GE 8-500 P
Connection thread	IT 1/4 inch
Max. cutting capacity in sheet metal	6 mm
Idle speed	500 rpm
Idle speed left	500 rpm
Power rating	200 W
Sound-pressure level	77 dB
Air consumption	4.5 l/s
Inner hose diameter	6 mm
Weight	1.2 kg
With right/left-hand rotation	Yes
Length	251 mm
Gross Weight	1.200 kg
Product Group	7AA

EAN

4251757300660