

Inductors for power circuits **Wound metal** SPM-HZR series(for automotive)











# SPM10054-HZR type













### FEATURES

- Magnetic shield type wound inductor for power circuits using a metallic magnetic material.
- Ocompared to ferrite wound type inductors, it is possible to achieve large current, low Rdc, and compactness.
- O Low inductance variance in high-temperature environments with good DC superimposition characteristics. -40 to 125°C (including self-temperature rise)
- O Metallic magnetic material is used, and the structure has an integrated molded coil, so hum noise is lower than with ferrite core adhesive coils.
- Operating temperature range: -40 to +125 °C (including self-temperature rise)
- Ocmpliant with AEC-Q200

### APPLICATION

O Automotive-related equipment (Car navigation, car audio)

### PART NUMBER CONSTRUCTION



### CHARACTERISTICS SPECIFICATION TABLE

L		Measuring frequency	DC resistance		Rated current*		Part No.
					Isat	Itemp	
(µH)	Tolerance	(kHz)	(mΩ)max.	(mΩ)typ.	(A)typ.	(A)typ.	
0.47	±20%	100	1.62	1.47	48.1	28.4	<u>SPM10054T-R47M-HZR</u>
0.68	±20%	100	2.09	1.90	40.8	24.0	<u>SPM10054T-R68M-HZR</u>
1.0	±20%	100	2.64	2.40	21.1	22.2	<u>SPM10054T-1R0M-HZR</u>
1.5	±20%	100	5.39	4.90	14.8	15.6	<u>SPM10054T-1R5M-HZR</u>
2.5	±20%	100	7.48	6.80	13.9	13.2	<u>SPM10054T-2R5M-HZR</u>
3.3	±20%	100	8.53	7.75	10.9	13.2	<u>SPM10054T-3R3M-HZR</u>
4.7	±20%	100	14.0	12.7	12.2	9.5	SPM10054T-4R7M-HZR
6.8	±20%	100	17.9	16.2	6.6	8.8	<u>SPM10054T-6R8M-HZR</u>
10.0	±20%	100	24.4	22.1	6.3	7.4	SPM10054T-100M-HZR
15.0	±20%	100	38.2	34.7	5.1	5.7	SPM10054T-150M-HZR
22.0	±20%	100	57.0	51.8	5.0	4.5	SPM10054T-220M-HZR
33.0	±20%	100	82.2	74.7	3.9	3.9	SPM10054T-330M-HZR
47.0	±20%	100	121.2	110.1	3.7	3.1	<u>SPM10054T-470M-HZR</u>
68.0	±20%	100	163.0	148.1	3.2	2.7	SPM10054T-680M-HZR

<sup>\*</sup> Rated current: smaller value of either lsat or Itemp.

Isat: When based on the inductance change rate (20% below the initial value)

Itemp: When based on the temperature increase (temperature increase of 40°C by self heating)

#### ■ Measurement equipment

Measurement item	Product No.	Manufacturer
L	4284A	Keysight Technologies
DC resistance	AX-111A	ADEX
Rated current Isat	4284A+42841A+42842C	Keysight Technologies


<sup>\*</sup> Equivalent measurement equipment may be used.





# SPM10054-HZR type

### ■ L FREQUENCY CHARACTERISTICS




### □測定器

Product No.	Manufacturer	
4294A	Keysight Technologies	

<sup>\*</sup> Equivalent measurement equipment may be used.

### ■ INDUCTANCE VS. DC BIAS CHARACTERISTICS



#### □測定器


Product No.	Manufacturer
4284A+42841A+42842C	Kevsight Technologies

<sup>\*</sup> Equivalent measurement equipment may be used.




# SPM10054-HZR type


### ■ SHAPE & DIMENSIONS




### PACKAGING STYLE



### RECOMMENDED LAND PATTERN



### ■ TAPE DIMENSIONS




Dimensions in mm

Туре	Α	В	K
SPM10054-HZR	10.5	11.5	5.6

### □ PACKAGE QUANTITY

Package quantity	500 pcs/reel



### ■ TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range *	Storage temperature range **	Individual weight
-40 to +125 °C	-40 to +125 °C	2 99 a

<sup>\*</sup> Operating temperature range includes self-temperature rise.

20221201

<sup>\*\*</sup> The storage temperature range is for after the assembly.



## REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

## **SAFETY REMINDERS**

Please pay sufficient attention to the warnings for safe designing when using this products

### REMINDERS

С	The storage period is within 12 months. Be sure to follow the storag less).	e conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH or
	If the storage period elapses, the soldering of the terminal electrodes	may deteriorate.
С	Do not use or store in locations where there are conditions such as ga	as corrosion (salt, acid, alkali, etc.).
С	Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature closes not exceed 150°C.	difference between the solder temperature and chip temperature
С	Soldering corrections after mounting should be within the range of the If overheated, a short circuit, performance deterioration, or lifespan sh	The state of the s
С	When embedding a printed circuit board where a chip is mounted to a overall distortion of the printed circuit board and partial distortion such	
С	Self heating (temperature increase) occurs when the power is turned design.	ed ON, so the tolerance should be sufficient for the set thermal
С	Carefully lay out the coil for the circuit board design of the non-magne A malfunction may occur due to magnetic interference.	etic shield type.
С	Use a wrist band to discharge static electricity in your body through the	e grounding wire.
С	Do not expose the products to magnets or magnetic fields.	
С	Do not use for a purpose outside of the contents regulated in the deliv	very specifications.
	The products described in this catalog are intended to be installed in telecommunications equipment, home appliances, amusement equipment measurement equipment, industrial robots) and to be used in automounted in a vehicle) or standard applications as general electronic egeneral electronic equipment in automotive applications in accordant while the said automotive or general electronic equipment including the usage methods, respectively. Other than automotive or automotive prothe applications listed below, whose performance and/or quality requimalfunction or defect could cause serious damage to society, person or Please understand that we are not responsible for any damage or liability or intend to use the products in the applications listed below or if yest forth in this specification, please contact us.	nent, computer equipment, personal equipment, office equipment, obiles (including the case where the said automotive product is equipment in automotive applications or standard applications as ce with the scope and conditions described in this specification he said product is intended to be used in the usual operation and oducts are not designed or warranted to meet the requirements of the same stringent level of safety or reliability, or whose failure for property.  Illity caused by use of the products in any of the applications below specification sheet.
	(1) Aerospace/aviation equipment	(7) Transportation control equipment
	(2) Transportation agricument (algebric trains, shine, etc.)	(9) Dublic information processing equipment

- (2) Transportation equipment (electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.