


Data sheet for General Purpose Toroidal Transformers – 225VA Encapsulated Series



Primary

Dual Primary winding for connection in series or parallel only.
 Input voltage : 115V or 230V +/-10% 50/60 Hz
 Dc resistance : 2 x 2,95Ohms +/-20% @ 20 °C
 Magnetising current : 15,7mA @ primary 230V 50Hz
 31,4mA @ primary 115V 50Hz

Losses

Iron loss : 1,85 Watts
 Copper loss : 15,86Watts
 Efficiency : 93% Typical
 Calculated Temperature rise : 50 °C
 (In open environment)
 Maximum rated ambient : 40 °C

Termination

All leads UL1015 or UL1569 rated 300V / 105°C
 Primary leads Double insulated with Insulation Class B tubes, minimum length 20mm
 Lead length Tolerance +/-10mm
 all lead ends 6mm tinned
 All Leads exit close to the outer top edge,

Temperature ratings

Winding wire : Class H (180 °C)
 Insulation System : Class B (130 °C)
 Leads insulation : Class A (105 °C)
 Encapsulation : Class A (105 °C)
 Overall : Class A
 Degrees of protection : IP20

Ordering code	Art. No.	Load voltage	No load voltage	Rated current	Secondary wire gauge	Sec. DC resistance Ohms @ 20 °C +/-20%
TI-044232-ME-EC	EC0225/12	2 x 12V	2 x 12,7V	2 x 9,38A	AWG12	2 x 0,05
TI-044233-ME-EC	EC0225/15	2 x 15V	2 x 15,9V	2 x 7,5A	AWG14	2 x 0,07
TI-044234-ME-EC	EC0225/18	2 x 18V	2 x 19,4V	2 x 6,25A	AWG14	2 x 0,10
TI-044235-ME-EC	EC0225/25	2 x 25V	2 x 26,9V	2 x 4,5A	AWG16	2 x 0,2
TI-044236-ME-EC	EC0225/30	2 x 30V	2 x 32,1V	2 x 3,75A	AWG16	2 x 0,3
TI-044237-ME-EC	EC0225/55	2 x 55V	2 x 58,7V	2 x 2,05A	AWG18	2 x 0,94

Approx. Dimensions

Diameter : 115mm
 Height : 54mm
 Center Hole suitable for M6 screw
 Weight : 2,5kg

Standards

Designed and manufactured in accordance with : EN61558-1 / EN61558-1/A1 / EN61558-2-4 or EN61558-2-6
 UL recognised under family approval E115159 to UL1411,UL60601-1,UL1950.

Marking

Model number xxxxxxxx ta40/A IP20
 Prim. 2 x 115V 50Hz (lead colours) 2xFuse XXAT
 Thermal fuse 125 °C
 Sec. 2 x rated voltage and rated current Amp (ref. Above table)(lead colours) 2xFuse XXAT
 Art. No. EC0120/XX

