

## Sling swivels, hoist rings

CARTEC

### Application:

Attachment point for lifting loads.

### Execution:

- Suitable for secure raising of loads according to Machinery Directive
- 2006/42/EC
- constructed, tested and certified according to GS-OA 15-04 - EN 1677
- DGUV certification
- Magnaflux crack tested to 100%
- can be rotated 360°

### Advantage:

- load direction 90°, with minimal space requirement
- Durable corrosion protection of screw
- designed for a load of 20,000 load changes



<b>Art. no.</b>	<b>77239 137</b>
<b>Brand</b>	CARTEC
<b>Manufacturer Part Number</b>	C806X36
<b>Thread dimension</b>	M36
<b>Load-carrying capacity</b>	8 t
<b>External width</b>	136 mm
<b>Internal width</b>	78 mm
<b>Width of support plate</b>	70 mm
<b>Bracket diameter</b>	28 mm
<b>Usable thread length</b>	59 mm
<b>Bracket height</b>	190 mm
<b>Width across flats</b>	55 mm
<b>Distance between lower edge of retainer holder and retainer</b>	81 mm
<b>Gross Weight</b>	5.900 kg
<b>Product Group</b>	775

### EAN

8013429871092