

Laser Infrared Thermometer

This compact easy-to-use infrared thermometer with Class II laser sighting is ideal for non-contact measurement of surface temperatures. Suitable for food preparation, plant & general maintenance, HVAC, transport & automotive, asphalt, health & safety, diesel and fleet maintenance.

- -50° to 350°C x 0.1°
- Measures °C or °F
- Just point, pull the trigger and read the display
- Class II laser to identify the centre point of the area being measured
- Distance to spot size ratio is 13 to 1 at the focal point
- Fixed emissivity at 0.95
- Response time less than 500 milliseconds
- 25mm LCD display with Backlight
- Automatic Data Hold when trigger released
- Min/Max memory
- Auto Power Off after 20 seconds of no activity
- Low Battery indication
- Back Light and Laser can be user disabled
- Impact-resistant ABS case
- Supplied with manual and battery

ACCESSORY

SCC-2 Soft Carry Pouch

Calibration Certificate

Issued at 5 points:

25°C, 50°C, 75°C, 100°C & 150°C

Additional points at:

£8.00 per point

From 25°C to 250°C

Technical Specifications

Range	-50° to +350°C
Resolution	0.1°C
Accuracy	±2% of reading ±2°C
Power	1 x 9V PP3 Alkaline Battery (LR-61)
Dimensions	160 x 99 x 28mm
Weight	176g