

DISPOSABLE GLOVES G-NITRILE

Item #	EAN	Product
844950	3660338074127	Powder Free
844951	3660338074134	
844952	3660338074141	
844953	3660338074158	
844954	3660338074165	

Description

Disposable glove, 0,06 mm nitrile, extra fingertip grip, powder, Cat. III, blue, approved for handling foodstuffs, latex-free, for precision work.

PROPERTIES

Extremely good fingertip sensitivity, extra flexible, good grip, good fit

Applications

FEATURES: Splash protection against chemicals, approved for handling foodstuffs

PRIMARY PROTECTION: Risk of infection, contact with dirt

PRIMARY ENVIRONMENTS OF USE: Disposable use, dirty environments

PRIMARY AREAS OF USE: Fine assembly, laboratory work, foodstuff handling, food handling

PRIMARY INDUSTRIES OF USE: Food processing, service

TYPE OF WORK: Light weight

Characteristics

- TYPE OF GLOVE: Disposable and/or chemical resistant gloves
- CATEGORY: Cat. III
- SIZE RANGE (EU): 7, 8, 9, 10, 11
- MATERIAL: Nitrile
- THICKNESS: 0,06 mm
- DEXTERITY: 5
- GRIP PATTERN: Extra fingertip grip
- LENGTH RANGE: 240 mm
- COLOUR: Blue
- AQL: 1.5



Standards and certifications EC TYPE EXAMINATION

Notified Body: 0493 Centexbel, Technologiepark 7, BE-9052 Zwijnaarde (Gent) Belgium

CHEMICAL RESISTANCE

According to EN 374-3. For details, please contact Ejendals

COMPLIANCE DESCRIPTION

EN 420:2003 + A1:2009 Protective gloves - general requirements and test methods

Council directive 89/686/EEC (PPE Directive)

EN 374-1:2016 Protective gloves against chemicals and micro-organisms - Part 2: Determination of resistance to penetration

EN 374-5:2016 Protective gloves against chemicals and micro-organisms - Part 3: Determination of resistance to permeation by chemicals

UK
CA

Permeation levels are based on breakthrough times as follows

Permeation level	1	2	3	4	5	6
Minimum breakthrough times (min)	10	30	60	120	240	480
Definition of breakthrough time through the glove palm (1ugm/cm ² /min)						

K: Sodium hydroxide 40% (CAS number 1310-73-2) - Permeation level 6

Packaging

- PIECES PER BOX: 100