

Extruded heatsinks for PCB mounting

SK 409 25,4 STS

45 x 12,7 mm, with solder pins and insulating ring




Features

Variants


Service

| | |
|------------------|--------------------|
| way of fixation | Schraubbefestigung |
| height | 12.7 mm |
| plate thickness | 3 mm |
| lengths | 25.4 mm |
| $R_{\theta j}$ | 8.2 K/W |
| drilling pattern | TO 220 |
| mounting method | with solder pin |
| surface | black anodised |





SK 409 38,1/50,8/63,5 STS

(1:1)
Sk 409 25,4 STS



SK 409 25,4 STS

(1:1)
SK 409 38,1/50,8/63,5 STS



| | | | | | |
|---|-------|------|---|------------------|---|
| <p style="text-align: center;">Schutzvermerk gemäß DIN ISO 16016 beachten © Fischer Elektronik GmbH & Co. KG 2005</p> | | | Freimasstoleranz DIN ISO 2768m | Oberfläche SA | Kunde 77777 - Fischer Elektronik |
| | | | | | fischer elektronik |
| | | | Datum | Name | Bezeichnung / Titel |
| | | | Erst. 26.06.2007 | | SK 409 ... STS |
| | | | Bearb. 16.02.2009 | Lochen Lochen | für Leiterplattenmontage mit Lötstiften |
| | | | Werkstoff / Material AlMgSi0,5 F22 (EN AW 6060 T66) | | Zeichnungs-Nummer |
| | | | | | 001020035 |
| Z. Änderungen | Datum | Name | C001020010.iam | | Maße in [] nach Profilltoleranzen nach DIN EN 12020 |
| | | | | | Blatt 1 |
| | | | | | Blätter 1 |

| Art.-Nr. | L (mm) |
|-----------------|--------|
| SK 409 25,4 STS | 25,4 |
| SK 409 38,1 STS | 38,1 |
| SK 409 50,8 STS | 50,8 |
| SK 409 63,5 STS | 63,5 |