



SBOS218A - DECEMBER 2001 - REVISED JUNE 2002

Stereo Audio Volume Control

FEATURES

 DIGITALLY-CONTROLLED ANALOG VOLUME CONTROL
 Two Independent Audio Channels
 Serial Control Interface

Serial Control Interface
Zero Crossing Detection
Mute Function

- WIDE GAIN AND ATTENUATION RANGE +31.5dB to -95.5dB with 0.5dB Steps
- LOW NOISE AND DISTORTION 120dB Dynamic Range 0.0004% THD+N at 1kHz (U-Grade) 0.0002% THD+N at 1kHz (A-Grade)
- NOISE-FREE LEVEL TRANSITIONS
- LOW INTERCHANNEL CROSSTALK –130dBFS
- POWER SUPPLIES: ±5V Analog, +5V Digital
- AVAILABLE IN DIP-16 AND SOL-16 PACKAGES
- PIN AND SOFTWARE COMPATIBLE WITH THE CRYSTAL CS3310

APPLICATIONS

- AUDIO AMPLIFIERS
- MIXING CONSOLES
- MULTI-TRACK RECORDERS
- BROADCAST STUDIO EQUIPMENT
- MUSICAL INSTRUMENTS
- EFFECTS PROCESSORS
- A/V RECEIVERS
- CAR AUDIO SYSTEMS

DESCRIPTION

The PGA2311 is a high–performance, stereo audio volume control designed for professional and high-end consumer audio systems. Using high performance operational amplifier stages internal to the PGA2311 yields low noise and distortion, while providing the capability to drive 600Ω loads directly without buffering. The 3-wire serial control interface allows for connection to a wide variety of host controllers, in addition to support for daisy-chaining of multiple PGA2311 devices.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.





ABSOLUTE MAXIMUM RATINGS(1)

Supply Voltage, V _A +
V _A 5.5V
V _D + +5.5V
V_A + to V_D +
Analog Input Voltage
Digital Input Voltage
Operating Temperature Range –40°C to +85°C
Storage Temperature Range65°C to +150°C
Junction Temperature
Lead Temperature (soldering, 10s) +300°C
Package Temperature (IR reflow, 10s) +235°C

 Stresses above these ratings may cause permanent damage. Exposure to absolute maximum conditions for extended periods may degrade device reliability.

ELECTROSTATIC DISCHARGE SENSITIVITY

This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

PACKAGE/ORDERING INFORMATION

PRODUCT	PACKAGE-LEAD	PACKAGE DESIGNATOR(1)	OPERATING TEMPERATURE RANGE	PACKAGE MARKING	ORDERING NUMBER	TRANSPORT MEDIA, QUANTITY
	DIP-16	N		PGA2311P	PGA2311P	Rails
PGA2311 (U-Grade)	001.40	5 144	-40°C to +85°C PGA2311U PGA2311U		Rails	
	SOL-16	DW		PGA2311U	PGA2311U/1K	Tape and Reel, 1000
	DIP-16	N		PGA2311PA	PGA2311PA	Rails
PGA2311 (A-Grade)		5	-40°C to +85°C	PGA2311UA	PGA2311UA	Rails
	SOL-16	DW		PGA2311UA	PGA2311UA/1K	Tape and Reel, 1000

⁽¹⁾ For the most current specifications and package information, refer to our web site at www. ti.com.

ELECTRICAL CHARACTERISTICS

At $T_A = +25^{\circ}C$, $V_{A+} = +5V$, $V_{A-} = -5V$, $V_{D+} = +5V$, $R_L = 100k\Omega$, $C_L = 20pF$, BW measure = 10Hz to 20kHz, unless otherwise noted.

		PGA23	PGA2311P, U (U-Grade).			PGA2311PA, UA (A-Grade)		
PARAMETER	CONDITIONS	MIN	TYP	MAX	MIN	TYP	MAX	UNITS
DC CHARACTERISTICS								
Step Size			0.5			0.5		dB
Gain Error	Gain Setting = 31.5dB		±0.05			±0.05		dB
Gain Matching			±0.05			±0.05		dB
Input Resistance			10			10		kΩ
Input Capacitance			3			3		pF
AC CHARACTERISTICS								
THD+N	$V_{IN} = 2Vrms, f = 1kHz$		0.0004	0.001		0.0002	0.0004	%
Dynamic Range	V _{IN} = AGND, Gain = 0dB	116	120		116	120		dB
Voltage Range, Output		(V _A –) + 1.25		(V _A +) – 1.25	(V _A –) + 1.25		(V _A +) – 1.25	V
Voltage Range, Input (without clipping)			2.5			2.5		Vrms
Output Noise	V _{IN} = AGND, Gain = 0dB		2.5	4		2.5	4	μVrms
Interchannel Crosstalk	f = 1kHz		-130			-130		dBFS
OUTPUT BUFFER								
Offset Voltage	V _{IN} = AGND, Gain = 0dB		0.25	0.5		0.25	0.5	mV
Load Capacitance Stability			100			100		pF
Short-Circuit Current			50			50		mA
Unity-Gain Bandwidth, Small Signal			10			10		MHz




 $\begin{tabular}{ll} \textbf{ELECTRICAL CHARACTERISTICS (Cont.)} \\ \textbf{At T}_{A} = +25^{\circ}\text{C}, \ V_{A}+ = +5\text{V}, \ V_{D}+ = +5\text{V}, \ R_{L} = 100\text{k}\Omega, \ C_{L} = 20\text{pF}, \ \text{BW measure} = 10\text{Hz to 20kHz}, \ \text{unless otherwise noted}. \\ \end{tabular}$

	001171710110	PGA2	311P, U (U-	-Grade)	PGA2311PA, UA (A-Grade)			
PARAMETER	CONDITIONS	MIN	MIN TYP MAX		MIN TYP		MAX	UNITS
DIGITAL CHARACTERISTICS								
High-Level Input Voltage, VIH		+2.0		V _D +	+2.0		V _D +	V
Low-Level Input Voltage, V _{IL}		-0.3		0.8	-0.3		0.8	V
High-Level Output Voltage, VOH	I _O = 200μA	(V _A +) – 1.0			(V _D +) – 1.0			V
Low-Level Output Voltage, VOL	$I_{O} = -3.2 \text{mA}$			0.4			0.4	V
Input Leakage Current			1	10		1	10	μΑ
SWITCHING CHARACTERISTICS								
Serial Clock (SCLK) Frequency	fSCLK	0		6.25	0		6.25	MHz
Serial Clock (SCLK) Pulse Width LOW	t _{PH}	80			80			ns
Serial Clock (SCLK) Pulse Width HIGH	t _{PL}	80			80			ns
MUTE Pulse Width LOW	tMI	2.0			2.0			ms
Input Timing	1411							
SDI Setup Time	tSDS	20			20			ns
SDI Hold Time	t _{SDH}	20			20			ns
CS Falling to SCLK Rising	tCSCR	90			90			ns
SCLK Falling to CS Rising	tCFCS	35			35			ns
Output Timing	0.00							
CS LOW to SDO Active	tcso			35			35	ns
SCLK Falling to SDO Data Valid	tCFDO			60			60	ns
CS HIGH to SDO High Impedance	tCSZ			100			100	ns
POWER SUPPLY								
Operating Voltage								
V _A +		+4.75	+5	+5.25	+4.75	+5	+5.25	V
V _A -		-4.75	- 5	-5.25	-4.75	- 5	-5.25	V
V _D +		+4.75	+5	+5.25	+4.75	+5	+5.25	V
Quiescent Current								
I _A +	$V_A + = +5V$		8	10		8	10	mA
IA-	V _A = -5V		10	12		10	12	mA
ID+	$V_{D} + = +5V$		0.5	1.0		0.5	1.0	mA
Power-Supply Rejection Ratio PSRR (250Hz)			100			100		dB
TEMPERATURE RANGE								
Operating Range		-40		+85	-40		+85	°C
Storage Range		-65		+150	-65		+150	°C
Thermal Resistance, _{JC}								
DIP-16			60			60		°C/W
SOL-16			50			50		°C/W



PIN CONFIGURATION




PIN ASSIGNMENTS

PIN	NAME	FUNCTION
1	ZCEN	Zero Crossing Enable Input (Active HIGH)
2	CS	Chip Select Input (Active LOW)
3	SDI	Serial Data input
4	V _D +	Digital Power Supply, +5V
5	DGND	Digital Ground
6	SCLK	Serial Clock Input
7	SDO	Serial Data Output
8	MUTE	Mute Control Input (Active LOW)
9	VINR	Analog Input, Right Channel
10	AGNDR	Analog Ground, Right Channel
11	VoutR	Analog Output, Right Channel
12	V _A +	Analog Power Supply, +5V
13	VA-	Analog Power Supply, –5V
14	VouTL	Analog Output, Left Channel
15	AGNDL	Analog Ground, Left Channel
16	V _{IN} L	Analog Input, Left Channel



TYPICAL CHARACTERISTICS


At $T_A = +25^{\circ}C$, $V_A + = +5V$, $V_A - = -5V$, $V_D + = +5V$, $R_L = 100k\Omega$, $C_L = 20pF$, BW measure = 10Hz to 20kHz, unless otherwise noted. (NOTE: All plots taken with PGA2311 A–Grade.)







TYPICAL CHARACTERISTICS (CONT.)

At T_A = +25°C, V_A + = +5V, V_A - = -5V, V_D + = +5V, R_L = 100k Ω , C_L = 20pF, BW measure = 10Hz to 20kHz, unless otherwise noted. (NOTE: All plots taken with PGA2311 A–Grade.)









GENERAL DESCRIPTION

The PGA2311 is a stereo audio volume control. It may be used in a wide array of professional and consumer audio equipment. The PGA2311 is fabricated in a submicron CMOS process.

The heart of the PGA2311 is a resistor network, an analog switch array, and a high–performance op amp stage. The switches are used to select taps in the resistor network that, in turn, determine the gain of the amplifier stage. Switch selections are programmed using a serial control port. The serial port allows connection to a wide variety of host controllers. Figure 1 shows a functional block diagram of the PGA2311.

POWER-UP STATE

On power up, "power–up reset" is activated for about 100ms during which the circuit is in hardware MUTE state and all internal flip-flops are reset. At the end of this period, the offset calibration is initiated without any external signals. Once this has been completed, the gain byte value for both the left and right channels are set to 00_{HEX}, or the software MUTE condition. The gain will remain at this setting until the host controller programs new settings for for each channel via the serial control port.

If during normal operation the power supply voltage drops below ±3.2V, the circuit enters a hardware MUTE state. A power-up sequence will be initiated if the power supply voltage returns to greater than ±3.2V.

ANALOG INPUTS AND OUTPUTS

The PGA2311 includes two independent channels, referred to as the left and right channels. Each channel has a corresponding input and output pin. The input and output pins are unbalanced, or referenced to analog ground (either AGNDR or AGNDL). The inputs are named V_{INR} (pin 9) and V_{INL} (pin 16), while the outputs are named V_{OUTR} (pin 11) and V_{OUTL} (pin 14).

The input and output pins may swing within 1.25V of the analog power supplies, V_A+ (pin 12) and V_A- (pin 13). Given $V_A+=+5V$ and $V_A-=-5V$, the maximum input or output voltage range is 7.5Vp-p.

For optimal performance, it is best to drive the PGA2311 with a low source impedance. A source impedance of 600Ω or less is recommended. Source impedances up to $2k\Omega$ will cause minimal degradation of THD+N. Please refer to the "THD+N vs Source Impedance" plot in the Typical Characteristics section of the datasheet.




Figure 1. PGA2311 Block Diagram.



SERIAL CONTROL PORT

The serial control port is utilized to program the gain settings for the PGA2311. The serial control port includes three input pins and one output pin. The inputs include \overline{CS} (pin 2), SDI (pin 3), and SCLK (pin 6). The sole output pin is SDO (pin 7).

The $\overline{\text{CS}}$ pin functions as the chip select input. Data may be written to the PGA2311 only when $\overline{\text{CS}}$ is LOW. SDI is the serial data input pin. Control data is provided as a 16-bit word at the SDI pin, 8 bits each for the left and right channel gain settings.

Data is formatted as MSB first, straight binary code. SCLK is the serial clock input. Data is clocked into SDI on the rising edge of SCLK.

SDO is the serial data output pin, and is used when daisy-chaining multiple PGA2311 devices. Daisy-chain operation is described in detail later in this section. SDO is a tri-state output, and assumes a high impedance state when $\overline{\text{CS}}$ is HIGH.

The protocol for the serial control port is shown in Figure 2. See Figure 3 for detailed timing specifications for the serial control port.




Figure 2. Serial Interface Protocol.



GAIN SETTINGS

The gain for each channel is set by its corresponding 8-bit code, either R[7:0] or L[7:0] (see Figure 2). The gain code data is straight binary format. If we let N equal the decimal equivalent of R[7:0] or L[7:0], then the following relationships exist for the gain settings:

For N = 0:

Mute Condition. The input multiplexer is connected to analog ground (AGNDR or AGNDL).

For N = 1 to 255:

Gain (dB) =
$$31.5 - [0.5 \text{ w} (255 - \text{N})]$$

This results in a gain range of +31.5dB (with N = 255) to -95.5dB (with N = 1).

Changes in gain setting may be made with or without zero crossing detection. The operation of the zero crossing detector and timeout circuitry is discussed later in this data sheet.




Figure 3. Serial Interface Timing Requirements.



DAISY-CHAINING MULTIPLE PGA2311 DEVICES

In order to reduce the number of control signals required to support multiple PGA2311 devices on a printed circuit board, the serial control port supports daisy-chaining of multiple PGA2311 devices. Figure 4 shows the connection requirements for daisy-chain operation. This arrangement allows a 3-wire serial interface to control many PGA2311 devices.

As shown in Figure 4, the SDO pin from device #1 is connected to the SDI input of device #2, and is repeated for additional devices. This in turn forms a large shift register, in which gain data may be written for all PGA2311s connected to the serial bus. The length of the shift register is 16 • N bits, where N is equal to the number of PGA2311 devices included in the chain. The $\overline{\text{CS}}$ input must remain LOW for 16 • N SCLK periods, where N is the number of devices connected in the chain, in order to allow enough SCLK cycles to load all devices.

ZERO CROSSING DETECTION

The PGA2311 includes a zero crossing detection function that can provide for noise-free level transitions. The concept is to change gain settings on a zero crossing of the input signal, thus minimizing audible glitches. This function is enabled or disabled using the ZCEN input (pin 1). When ZCEN is LOW, zero crossing detection is disabled. When ZCEN is HIGH, zero crossing detection will be enabled.

The zero crossing detection takes effect with a change in gain setting for a corresponding channel. The new gain setting will not be implemented until either positive slope zero crossing is detected or a time-out period of 16ms has elapsed. In the case of a time-out, the new gain setting takes effect with no attempt to minimize audible artifacts.




Figure 4. Daisy-Chaining Multiple PGA2311 Devices.



MUTE FUNCTION

Muting can be achieved by either hardware or software control. Hardware muting is accomplished via the MUTE input, and software muting by loading all zeroes into the volume control register.

 $\overline{\text{MUTE}}$ disconnects the internal buffer amplifiers from the output pins and terminates A_{OUT}L and A_{OUT}R with 10kΩ resistors to ground. The mute is activated with a zero crossing detection (independent of the zero cross enable status) or an 16ms time-out to eliminate any audible "clicks" or "pops". $\overline{\text{MUTE}}$ also initiates an internal offset calibration.

A software mute is implemented by loading all zeroes into the volume control register. The internal amplifier is set to unity gain with the amplifier input connected to AGND.

APPLICATIONS INFORMATION

This section includes additional information that is pertinent to designing the PGA2311 into an end application.

RECOMMENDED CONNECTION DIAGRAM

Figure 5 depicts the recommended connections for the PGA2311. Power-supply bypass capacitors should be placed as close to the PGA2311 package as physically possible.




Figure 5. Recommended Connection Diagram.



PRINTED CIRCUIT BOARD (PCB) LAYOUT GUIDELINES

It is recommended that the ground planes for the digital and analog sections of the PCB be separate from one another. The planes should be connected at a single point. Figure 6 shows the recommended PCB floor plan for the PGA2311. The PGA2311 is mounted so that it straddles the split between the digital and analog ground planes. Pins 1 through 8 are oriented to the digital side of the board, while pins 9 through 16 are on the analog side of the board.




Figure 6. Typical PCB Layout Floor Plan.

PLASTIC DUAL-IN-LINE PACKAGE

0.850

0.940



PACKAGE DRAWINGS

MPDI002B ± JANUARY 1995 ± REVISED FEBRUARY 2000


N (R-PDIP-T**)

16 PINS SHOWN

16

PINS ** 14 16 18 20 MAX 0.775 0.775 0.920 0.975 (19,69) (19,69) (23,37) (24,77)

0.745



DIM

A MAX

0.745

- NOTES: A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - C. Falls within JEDEC MS-001 (20-pin package is shorter than MS-001).

9




PACKAGE DRAWINGS (Cont.)

MSOI003E - JANUARY 1995 - REVISED SEPTEMBER 2001

DW (R-PDSO-G**)

16 PINS SHOWN

PLASTIC SMALL-OUTLINE PACKAGE



- NOTES: A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
 - D. Falls within JEDEC MS-013

PACKAGE OPTION ADDENDUM



i.com 26-Mar-2007

PACKAGING INFORMATION

Orderable Device	Status ⁽¹⁾	Package Type	Package Drawing	Pins	Package Qty	e Eco Plan ⁽²⁾	Lead/Ball Finish	MSL Peak Temp ⁽³⁾
PGA2311P	ACTIVE	PDIP	N	16	25	Green (RoHS & no Sb/Br)	CU NIPDAU	N / A for Pkg Type
PGA2311PA	ACTIVE	PDIP	N	16	25	Green (RoHS & no Sb/Br)	CU NIPDAU	N / A for Pkg Type
PGA2311PAG4	ACTIVE	PDIP	N	16	25	Green (RoHS & no Sb/Br)	CU NIPDAU	N / A for Pkg Type
PGA2311PG4	ACTIVE	PDIP	N	16	25	Green (RoHS & no Sb/Br)	CU NIPDAU	N / A for Pkg Type
PGA2311U	ACTIVE	SOIC	DW	16	48	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR
PGA2311U/1K	ACTIVE	SOIC	DW	16	1000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR
PGA2311U/1KG4	ACTIVE	SOIC	DW	16	1000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR
PGA2311UA	ACTIVE	SOIC	DW	16	48	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR
PGA2311UA/1K	ACTIVE	SOIC	DW	16	1000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR
PGA2311UA/1KG4	ACTIVE	SOIC	DW	16	1000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR
PGA2311UAG4	ACTIVE	SOIC	DW	16	48	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR
PGA2311UG4	ACTIVE	SOIC	DW	16	48	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.



PACKAGE OPTION ADDENDUM

26-Mar-2007

In no event shall TI's liabil	lity arising out of such inform	ation exceed the total nu	urchase price of the TI pa	art(e) at issue in this do	oument sold by T
to Customer on an annual	lity arising out of such inform I basis.	allon exceed the total po	inchase price of the 11 pa	int(s) at issue in this uc	cument sold by T

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
Low Power Wireless	www.ti.com/lpw	Telephony	www.ti.com/telephony
		Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2007, Texas Instruments Incorporated