



XNT Soldering Tip Family

- + Most difficult, high mass soldering jobs
- + Maximum power and response for top performance
- + Optimal balance between power, control and running costs with wide range of tips
- + Highest quality soldering standard for widest range of applications



	Article	a / b (mm) / (inch)	Article	a / b (mm) / (inch)	Article	a / b (mm) / (inch)	
Chisel 	XNT A T0054485199 BESTSELLER	1.6 mm / 0.4 mm 0.063 inch / 0.016 inch	XNT CS T0054487099	3.2 mm / 0.8 mm 0.126 inch / 0.315 inch	XNT MX T0054488399	3.2 mm / 0.8 mm 0.126 inch / 0.315 inch	
	XNT AX T0054486499	1.6 mm / 0.8 mm 0.063 inch / 0.315 inch	XNT D T0054485399	4 mm / 0.8 mm 0.157 inch / 0.315 inch	XNT 6 T0054485699	1.6 mm / 0.4 mm 0.063 inch / 0.016 inch	
	XNT B T0054485799 BESTSELLER	2.4 mm / 0.8 mm 0.094 inch / 0.315 inch	XNT H T0054485999 BESTSELLER	0.8 mm / 0.4 mm 0.031 inch / 0.016 inch	XNT 1SC T0054486299 BESTSELLER	0.4 mm / 0.15 mm 0.016 inch / 0.006 inch	
	XNT BX T0054488299	2.4 mm / 0.8 mm 0.094 inch / 0.315 inch	XNT K T0054486099	1.2 mm / 0.4 mm 0.047 inch / 0.016 inch	XNT 1SCNW T0054488199	0.3 mm / 0.1 mm 0.012 inch / 0.004 inch	
	XNT C T0054485899 only US	3.2 mm / 0.8 mm 0.126 inch / 0.315 inch	XNT L T0054486699	3.2 mm / 0.8 mm 0.126 inch / 0.315 inch	XNT 4X 45° T0054487499	1.2 mm / 0.4 mm 0.047 inch / 0.016 inch	
Round 	XNT 1L T0054487199	0.2 mm 0.008 inch	XNT 4 T0054485599	1.2 mm 0.047 inch	High mass soldering jobs 	Power Response 	Heat up time °C -350 -300 -200 -100 0 5 Sec.* *from 50°C to 350°C / 120°F to 620°F
	XNT 1LX T0054487299	0.2 mm 0.008 inch	XNT AA 45° T0054488499	1.6 mm 0.063 inch			
	XNT 1S T0054485299	0.2 mm 0.008 inch	XNT BB 45° T0054488599	2.4 mm 0.094 inch			
	XNT 1SLX 45° T0054487599	0.4 mm 0.016 inch	XNT CC 45° T0054488699	3.2 mm 0.126 inch			
	XNT 1X T0054486599	0.4 mm 0.016 inch	XNT F 45° T0054488799	1.2 mm 0.047 inch			
	XNT AS T0054486999 only US	1.6 mm 0.063 inch					
Conical 	XNT 1 T0054485099 BESTSELLER	0.5 mm 0.02 inch	Measuring tip Measuring tip T0054486199N 				
	XNT S T0054486899	0.4 mm 0.016 inch					
Gullwing 	XNT GW1 T0054485499	1.6 mm 0.063 inch					
	XNT GW2 short T0054488099	1.0 mm 0.039 inch					
Knife 	XNT KN T0054486399	2.0 mm 0.079 inch					



Weller®

weller-tools.com/toolselector/en
weller-tools.com/toolselector/us

Fume Extraction Solution

Providing clean air in your workplace

Fume Extraction solution protect your health



90 minutes soldering with lead-free solder wire

Why fume extraction? See the movie on www.youtube.com/wellersoldering



Weller®



Owning The Bench

Everything from a single source from Weller

1-STOP-SOLUTION PROVIDER

Fume Extraction Units

Soldering accessories


Soldering equipment

Solder wire

Swiss Made

Product Registration

Get access to the support, warranty and updates



weller-tools/productsregistration/en

GERMANY Weller Tools GmbH Carl-Benz-Strasse 2 74354 Besigheim Tel: +49 (0)7143 580-0 Fax: +49 (0)7143 580-108	USA Apex Tool Group, LLC 670 Industrial Drive Lexington, SC 29072 Tel: +1 (800) 688-8949 Fax: +1 (800) 234-0472	CHINA Apex Tool Group Room 302A, NO 177 Bibo Road Shanghai, 201203 Tel: +86 (21) 60880288 Fax: +86 (21) 60880289
---	---	--

www.weller-tools.com
© 2019, Apex Tool Group, LLC.
Weller® is a registered trademark and registered Design of Apex Tool Group, LLC.
T0055749100 / 09.2019



Weller® Erem

High Precision cutters and tweezers

Erem® is a leader in the development and production of high-precision, top-quality hand tools (side and tip cutters, pliers and tweezers).
Founded in Geneva, Switzerland in 1963, Erem® precision tools are the result of ongoing product development and innovation to meet customer demands and the requirements of modern manufacturing techniques.



- Explore our Erem premium precision tools
- Highest of Quality**
The quality and performance of Erem® precision tools are the result of over 50 years of development and know-how.
- Made in Switzerland since 1963**
Produced in Bevaix at Lake Neuchâtel, Erem® tools meet the demanding requirements that define Swiss quality.
- Hand-crafted**
Each tool is ground individually by hand and checked for quality compliance.
- Patented Erem® technology**
The patented Magic Spring guarantees a constant spring force for more than 1 million operations.

Discover more

The Original

Genuine Weller tip quality



- Why use Weller tips?**
- ✓ Tool protection – Protects soldering iron from irreparable damage
 - ✓ Optimal performance – Designed for excellent heat transfer to deliver ideal soldering joints
 - ✓ Cost savings – Consistent performance reduces rework

Look for Genuine Weller tips:


- ✓ Seal of Quality on packaging
- ✓ Weller logo on tips




More cleaning tips

Weller Heating Technologies

Concentrated power at the tip



Weller TECHNOLOGY OVERVIEW



Discover more

WT1010 Bundle

Test & get your hands on Premium Precision Tools.



Explore our Erem premium precision tools

Poster inside

Weller®
weller-tools.com