XCMN2102L1

limit switch XCMN - steel roller plunger - 1NC +1NO - snap - 1 m





Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch
Device short name	XCMN
Sensor design	Miniature
Body type	Fixed
Head type	Plunger head
Material	Plastic
Body material	Plastic
Head material	Zamak
Fixing mode	By the body
Movement of operating head	Linear
Type of operator	Spring return roller plunger metal
Type of approach	Lateral approach, 2 directions
Number of poles	2
Contacts type and composition	1 NC + 1 NO
Contact operation	Snap action

Complementary

Switch actuation	By 30° cam
Electrical connection	Fixed cable
Cable length	3.28 ft (1 m)
Cable composition	4 x 0.75 mm²
Wire insulation material	PvR
Contacts insulation form	Zb
Positive opening	With
Positive opening minimum force	35 N
Minimum force for tripping	7 N
Maximum actuation speed	1.64 ft/s (0.5 m/s)
Contact code designation	B300, AC-15 (Ue = 240 V), le = 1.5 A EN/IEC 60947-5-1 appendix A R300, DC-13 (Ue = 250 V), le = 0.1 A EN/IEC 60947-5-1 appendix A
[Ui] rated insulation voltage	300 V 3)UL 508 400 V 3)IEC 60947-5-1 300 V 3)CSA C22.2 No 14
Maximum resistance across terminals	25 MOhm IEC 60255-7 category 3
[Uimp] rated impulse withstand voltage	4 KV IEC 60664 4 kV IEC 60947-1
Short-circuit protection	6 A cartridge fuse gG
Electrical durability	5000000 Cycles, DC-13, 120 V, 1 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 Cycles, DC-13, 24 V, 3 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 cycles, DC-13, 48 V, 2 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C
Mechanical durability	5000000 cycles
Maximum Width	1.18 in (30 mm)
Height	2.77 in (70.4 mm)
Depth	0.63 in (16 mm)
Net Weight	0.18 lb(US) (0.08 kg)

Environment

Shock resistance	25 gn 18 ms IEC 60068-2-27
Vibration resistance	5 gn 10500 Hz)IEC 60068-2-6
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK04 EN 50102
Electrical shock protection class	Class II IEC 61140 Class II NF C 20-030
Ambient air temperature for operation	-13158 °F (-2570 °C)
Ambient air temperature for storage	-40158 °F (-4070 °C)
Protective treatment	TC
Product certifications	CSA CCC UL
Standards	CSA C22.2 No 14 UL 508 EN/IEC 60204-1 EN/IEC 60947-5-1

Ordering and shipping details

22413 - LIMIT SWITCH, IEC, MINIATURE
Т
00785901704881
1
0.26 lb(US) (0.12 kg)
Yes
ID

Packing Units

Package 1 Height	0.200 dm
Package 1 width	1.300 dm
Package 1 Length	1.300 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	☑ REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EEU RoHS Declaration
Mercury free	Yes
RoHS exemption information	₫Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	☑ End Of Life Information


Contractual warranty

Warranty	18 months

Product data sheet **Dimensions Drawings**

XCMN2102L1

Dimensions




- (1) 2 fixing holes Ø 4.2 mm, counterbored Ø 8 mm by 4 mm deep.
 (2) External diameter 7.5 mm.

Product data sheet Mounting and Clearance

XCMN2102L1

Mounting

Sweep of Connecting Cable



(1) Recommended

) To be avoided

Setting-up

Plunger or Multi-directional Heads




Product data sheet Connections and Schema

XCMN2102L1

Wiring diagram

2-pole NC + NO Snap Action



(BK) Black (BK- Black White WH)

(BN) Brown

(BU) Blue

Product data sheet **Technical Description**


XCMN2102L1

Characteristics of Actuation

Switch Actuation by 30° Cam



Functionnal Diagram



- Positive opening point
- (A) Cam displacement
- (1) NC contact with positive opening operation
- Closed
- (2) (3) Open
- (4) Tripping (5) Resetting
- (BK) Black
- (BK- Black White
- ÙΗ)
- (BN) Brown
- (BU) Blue