



PLUG-IN RELAY COMPACT UNIT 24V DC, 1 CO LED
MODULE RED SOCKET W. LOGIC ISOLATION PLUG-
IN TERMINAL (PUSH-IN)

Figure similar

General technical data:

Type of voltage		DC
Control supply voltage		
<ul style="list-style-type: none"> • for DC Rated value — minimum — maximum 	V	24
	V	24
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		1
Operating current of the auxiliary contacts		
<ul style="list-style-type: none"> • at AC-15 — at 230 V 	A	3
Design of the switching function positively driven		No
Switching behavior		monostable


Mechanical data:

Type of electrical connection		spring-loaded terminals
Design of the relay operating mechanism		poled
Product component Plug-in socket		Yes
Width	mm	15.5
Height	mm	71
Depth	mm	98

Certificates/ approvals:



Further information

Industry Mall (Online ordering system)<http://www.siemens.com/industrymall>**Cax online generator**<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=LZS:RT3D4L24>**Information- and Downloadcenter (Catalogs, Brochures,...)**<http://www.siemens.com/industrial-controls/catalogs>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<https://support.industry.siemens.com/cs/ww/en/ps/LZS:RT3D4L24>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=LZS:RT3D4L24&lang=en

last modified:

15.01.2015