

Double-sided cantilever rack

RAL 5010



Application:

Cantilever racks are the perfect solution for vertically or horizontally storing all types of long goods and for storing sheet and panel stock. META offers two cantilever solutions, the **META ATLAS ST** and the **META MULTISTRONG**. This means there are options for everything - from small, compact shelving rows for light to medium-weight long goods to towering cantilever racks for heavy profiles and sheet goods.

The **META ATLAS ST** comes in two versions. The cantilever rack is equipped with cantilevers of the same length. Whereas the long goods rack is equipped with cantilevers of different lengths, the lengths of which are progressively shortened towards the top.

The boltless **META MULTISTRONG** rack is available in two versions, Light and Medium. We offer the **META MULTISTRONG Heavy** as a bolted version. The versions differ in their cantilever load, Light = up to 220 kg, Medium = up to 535 kg and Heavy = up to 1,960 kg. With this professional system, customers can choose between different dimensional variants.

Execution:

- Add-on rack, for expanding the basic rack
- For vertically/horizontally storing long goods and storing sheet and panel stock
- Hot-rolled IPE profiles perforated on both sides for subsequent conversion from single-sided to double-sided, only the base section would need to be replaced
- Sturdy top-class branded quality
- Anti-lift mechanism reliably secures the cantilevers against unintentional removal when goods are stored or removed
- The base load capacity is up to 5 times the load capacity of the cantilever arms
- Planning dimensions basic shelf: Length = axis diameter + 64 mm, depth = nominal depth + 210 mm
- Foot load = 5 times arm load

Advantage:

- Different versions available
- Built-in extension options and precisely dimensioned, customised solutions
- Quick access to goods

Art. no.	50192 167
Brand	META
Manufacturer Part Number	20075141
Height	3000 mm
Length	1000 mm
Depth	800 mm
Type of shelving	Add-on shelving
Design	Double-sided
Colour	Gentian blue RAL 5010
Surface	Powder-coated
ESD-capable	No
Design of the frame	Disassembled
Quality label	RAL-RG 614/5
Number of arms	5 PCS
Dimension between axes	1030 mm
One-sided stand load	1250 kg
Load-carrying capacity per arm	250 kg
Material	Steel
Gross Weight	99.374 kg
Product Group	508

EAN

4026212120363