## **Fiber-Optic Cable Sensor**


# UC88PCV3

Part Number



- Adaptable for glass fiber-optic cables: reflex and through-beam mode
- Adjustable detection range
- Stainless steel housing
- Very large detection range

These sensors are equipped for use with glass fiber optic cables but can be used with or without one. The transmitter and receiver are located in a single housing. The sensor evaluates transmitted light reflected back from the object and the output is switched as soon as an object passes the selected range. Bright objects reflect more light than dark objects, and can thus be recognized from greater distances.



#### **Technical Data**


| Optical Data                               |                 |  |  |  |  |
|--|-----------------|--|--|--|--|
| Range 2000 mm                              |                 |  |  |  |  |
| Switching Hysteresis                       | < 15 %          |  |  |  |  |
| Light Source                               | Infrared Light  |  |  |  |  |
| Service Life (T = +25 °C)                  | 100000 h        |  |  |  |  |
| Max. Ambient Light                         | 10000 Lux       |  |  |  |  |
| Opening Angle                              | 12 °            |  |  |  |  |
| Electrical Data                            |                 |  |  |  |  |
| Supply Voltage                             | 1030 V DC       |  |  |  |  |
| Current Consumption (Ub = 24 V)            | < 50 mA         |  |  |  |  |
| Switching Frequency                        | 500 Hz          |  |  |  |  |
| Response Time                              | 1 ms            |  |  |  |  |
| Temperature Drift                          | < 10 %          |  |  |  |  |
| Temperature Range                          | -2560 °C        |  |  |  |  |
| Switching Output Voltage Drop              | < 2,5 V         |  |  |  |  |
| PNP Switching Output/Switching Current     | 200 mA          |  |  |  |  |
| Residual Current Switching Output          | < 50 μA         |  |  |  |  |
| PNP Contamination Output/Switching Current | 50 mA           |  |  |  |  |
| Short Circuit Protection                   | yes             |  |  |  |  |
| Reverse Polarity Protection                | yes             |  |  |  |  |
| Overload Protection                        | yes             |  |  |  |  |
| Protection Class                           | III             |  |  |  |  |
| Mechanical Data                            |                 |  |  |  |  |
| Setting Method                             | Potentiometer   |  |  |  |  |
| Housing Material                           | Stainless Steel |  |  |  |  |
| Full Encapsulation                         | yes             |  |  |  |  |
| Degree of Protection                       | IP67            |  |  |  |  |
| Connection                                 | M12 × 1; 4-pin  |  |  |  |  |
| Contamination Output                       |                 |  |  |  |  |
| PNP NO/NC switchable                       |                 |  |  |  |  |
| Connection Diagram No.                     | 105             |  |  |  |  |
| Control Panel No.                          | D5              |  |  |  |  |
| Suitable Connection Equipment No.          | 2               |  |  |  |  |
| Suitable Mounting Technology No.           | 150             |  |  |  |  |
| Suitable Fiber-Optic Cable Adapter No.     | 02              |  |  |  |  |

### **Complementary Products**


Glass Fiber-Optic Cable

PNP-NPN Converter BG2V1P-N-2M






#### Ctrl. Panel



- 01 = Switching Status Indicator
- 02 = Contamination Warning
- 05 = Switching Distance Adjuster
- 08 = NO/NC Switch



| Legen    | d                                   |          | PT       | Platinum measuring resistor    | ENARS | Encoder A/Ā (TTL)               |
|----------|-------------------------------------|----------|----------|--------------------------------|-------|---------------------------------|
| +        | Supply Voltage +                    |          | nc       | not connected                  | ENBRS | Encoder B/B (TTL)               |
| -        | Supply Voltage 0 V                  |          | U        | Test Input                     | ENA   | Encoder A                       |
| ~        | Supply Voltage (AC Voltage)         |          | Ū        | Test Input inverted            | ENB   | Encoder B                       |
| Α        |                                     | 10)      | W        | Trigger Input                  | Amin  | Digital output MIN              |
| Ā        | Switching Output (N                 | 1C)      | W -      | Ground for the Trigger Input   | Амах  | Digital output MAX              |
| V        |                                     | 10)      | 0        | Analog Output                  | Аок   | Digital output OK               |
| V        | Contamination/Error Output (N       | 1C)      | 0-       | Ground for the Analog Output   | SY In | Synchronization In              |
| E        | Input (analog or digital)           |          | BZ       | Block Discharge                | SY OL | T Synchronization OUT           |
| Т        | Teach Input                         |          | Awv      | Valve Output                   | OLT   | Brightness output               |
| Z        | Time Delay (activation)             |          | а        | Valve Control Output +         | М     | Maintenance                     |
| S        | Shielding                           |          | b        | Valve Control Output 0 V       | rsv   | reserved                        |
| RxD      | Interface Receive Path              |          | SY       | Synchronization                | Wire  | Colors according to DIN IEC 757 |
| TxD      | Interface Send Path                 |          | SY-      | Ground for the Synchronization | BK    | Black                           |
| RDY      | Ready                               |          | E+       | Receiver-Line                  | BN    | Brown                           |
| GND      | Ground                              |          | S+       | Emitter-Line                   | RD    | Red                             |
| CL       | Clock                               |          | <b>±</b> | Grounding                      | OG    | Orange                          |
| E/A      | Output/Input programmable           |          | SnR      | Switching Distance Reduction   | YE    | Yellow                          |
| •        | IO-Link                             |          | Rx+/-    | Ethernet Receive Path          | GN    | Green                           |
| PoE      | Power over Ethernet                 |          | Tx+/-    | Ethernet Send Path             | BU    | Blue                            |
| IN       | Safety Input                        |          | Bus      | Interfaces-Bus A(+)/B(-)       | VT    | Violet                          |
| OSSD     | Safety Output                       |          | La       | Emitted Light disengageable    | GY    | Grey                            |
| Signal   | Signal Output                       |          | Mag      | Magnet activation              | WH    | White                           |
|          | Ethernet Gigabit bidirect, data lii | ne (A-D) |          | Input confirmation             | PK    | Pink                            |
| ENors422 | Encoder 0-pulse 0-0 (TTL)           |          | EDM      | Contactor Monitoring           | GNY   | Green/Yellow                    |









