




## Twin Ferrules, Single Bag with insulating collar

For conductor cross sections from  
2 x 0.5 mm<sup>2</sup> up to 2 x 16 mm<sup>2</sup>  
(2 x AWG 20 up to 2 x AWG 6).

Material: tin-plated copper.

Tolerances according to DIN 46228 part 4



mm <sup>2</sup>	L <sub>2</sub>	Typ*	AWG	Item no./color code			Dim.	L <sub>1</sub>	L <sub>2</sub>	d <sub>1</sub>	S <sub>1</sub>	S <sub>2</sub>	A	B	Qty/bag
				Z+F	DIN	KDS									
2 x 0.50	8	N	2 x 20	V30AE001134	V30AE001145	V30AE001145	" mm 14	8	1.4	0.15	0.3	5.0	3.0	500	
2 x 0.50	10	HL	2 x 20	V30AE001135	V30AE001146	V30AE001146	" mm 16	10	1.4	0.15	0.3	5.0	3.0	500	
2 x 0.50	12	L	2 x 20	V30AE001136	V30AE001147	V30AE001147	" mm 18	12	1.4	0.15	0.3	5.0	3.0	500	
2 x 0.75	8	N	2 x 18	V30AE000606	V30AE000607	V30AE003106	" mm 14	8	1.7	0.15	0.3	5.5	3.0	500	
2 x 0.75	10	HL	2 x 18	V30AE000733	V30AE000734	V30AE003107	" mm 16	10	1.7	0.15	0.3	5.5	3.0	500	
2 x 0.75	18	L	2 x 18	V30AE000740	V30AE000741	V30AE003108	" mm 24	18	1.7	0.15	0.3	5.5	3.0	500	
2 x 1.00	8	N	2 x 17	V30AE000608	V30AE000609	V30AE000609	" mm 15	8	2.0	0.15	0.3	5.8	3.2	500	
2 x 1.00	12	HL	2 x 17	V30AE000735	V30AE000736	V30AE000736	" mm 19	12	2.0	0.15	0.3	5.8	3.2	500	
2 x 1.00	18	L	2 x 17	V30AE000742	V30AE000743	V30AE000743	" mm 25	18	2.0	0.15	0.3	5.8	3.2	500	
2 x 1.50	8	N	2 x 16	V30AE000623	V30AE000625	V30AE000625	" mm 16	8	2.2	0.15	0.3	6.5	3.6	500	
2 x 1.50	12	HL	2 x 16	V30AE000737	V30AE000738	V30AE000738	" mm 20	12	2.2	0.15	0.3	6.5	3.6	500	
2 x 1.50	18	L	2 x 16	V30AE000744	V30AE000745	V30AE000745	" mm 26	18	2.2	0.15	0.3	6.5	3.6	100	
2 x 2.50	10	N	2 x 14	V30AE000611	V30AE000611	V30AE003115	" mm 19	10	2.8	0.15	0.4	8.0	4.5	500	
2 x 2.50	12	HL	2 x 14	V30AE000748	V30AE000748	V30AE003116	" mm 21	12	2.8	0.15	0.4	8.0	4.5	100	
2 x 2.50	18	L	2 x 14	V30AE000750	V30AE000750	V30AE003117	" mm 27	18	2.8	0.15	0.4	8.0	4.5	100	
2 x 4.00	12	N	2 x 12	V30AE001148	V30AE001148	V30AE003118	" mm 22	12	3.5	0.20	0.5	9.0	5.2	100	
2 x 4.00	18	L	2 x 12	V30AE001149	V30AE001149	V30AE003119	" mm 28	18	3.5	0.20	0.5	9.0	5.2	100	
2 x 6.00	12	N	2 x 10	V30AE001139	V30AE001150	V30AE003120	" mm 23	12	4.5	0.20	0.5	11.4	6.2	100	
2 x 6.00	18	L	2 x 10	V30AE001140	V30AE001151	V30AE003121	" mm 29	18	4.5	0.20	0.5	11.4	6.2	100	
2 x 10.00	12	N	2 x 8	V30AE001141	V30AE001152	V30AE003122	" mm 24	12	5.8	0.20	0.5	13.4	7.6	100	
2 x 10.00	18	L	2 x 8	V30AE001142	V30AE001153	V30AE003123	" mm 30	18	5.8	0.20	0.5	13.4	7.6	100	
2 x 16.00	16	N	2 x 6	V30AE001143	V30AE001154	V30AE003124	" mm 29	16	8.3	0.30	0.6	17.2	9.5	50	
2 x 16.00	25	L	2 x 6	V30AE001144	V30AE001155	V30AE003125	" mm 38	25	8.3	0.30	0.6	17.2	9.0	50	

\* Explanation see page 1