Test leads

Modular test leads

Modular test leads provide the convenience of attaching clips, hooks and grabbers, as needed. All of these leads are 1.5 m (59 in) long, offer reinforced strain relief, and include banana jack terminations that allow a great variety of test lead configurations.









TL221 SureGrip™ Test Lead Extensions Set

One pair (red, black) siliconeinsulated leads with safetyshrouded, 4 mm (0.16 in) banana plugs.

- Couplers have female connectors on both ends
- Safety rating: CAT IV 600 V, CAT III 1000 V, 10 A

TL222 SureGrip™ Silicone Insulated Test Leads

One pair (red, black) silicone-insulated test leads (red, black) with safety-shrouded, 4 mm (0.16 in) banana plugs.

Right angle connectors on both ends

TL224 SureGrip™ Insulated Test Leads

One pair (red, black) siliconeinsulated test leads with safety-shrouded 4 mm (0.16 in) banana plugs.

- Right angle connector on one end and straight connector on the other
- Safety rating: CAT IV 600 V, CAT III 1000 V, 10 A

TL27 Heavy-duty Test Lead Set

One pair (red, black) rugged, EPDM-insulated test leads with safety-shrouded 4 mm (0.16 in) banana plugs.

- Straight connectors on both ends
- Safety rating: CAT III 1000 V, 10 A

Test lead holder



H900 Test Lead Holder

Heavy-duty holder for conveniently storing test lead wires.

- Mounting holes for securing to wall or other surfaces
- For test lead wires up to 8 mm (0.31 in) in diameter
- Overall dimensions (LxWxH): 27.9 cm x 8.9 cm x 3.2 cm (11 in x 3.5 in x 1.25 in)

