

## Doe laser, green, 532 nm, 5 mW

DOE263-532-5-3(16x90)-NT  
Order Number: 70111200

Main Parameters (*)	min	typ	max	Unit
Wavelength		532		nm
Optical Output Power		5		mW
Operating Voltage	2.7	3	3.3	V DC
Operating Current	125	250	375	mA
Operating Temperature	15		30	°C
Storage Temperature	-40		80	°C

### Main Data

Warranty 1 years

### Technical Parameters

Lifetime > 5,000 h  
RoHS yes

### Optical Parameters

Beam Shape	DOE
Laser Class	2M
Divergence	D - 0.5 mrad
Optics	acryl lense
Laser technology	Solid State (YVO4+KTP)
Stability	+/- 20% @ 15-30°C
Protection Lens	yes
Focus	fixed
Warm up time	< 15 min

### Electrical Parameters

Potential of Housing	VDD(+)
Connector	2.5 mm DC plug (GND pole inner)
Power Supply	LFNT-3-C

### Mechanical Parameters

Size	Ø16x90 mm
Material	aluminium
Cable length	1,360 mm
Output Aperture	6 mm
Housing Color	cyan
Weight	43 g

### DOE

Alpha	5.9 °
Beta	1.48 °
a	10.4 mm
b	2.6 mm
Diameter (without holder)	8 mm
Width (without Holder)	1.2 mm
Material	PC

(\*) Over the complete operating temperature range

## Features




- DOE Laser
- Image processing
- Laser Class 2M
- Compact size

## Picture



## Safety Label



## Valid Revision

1 | 27-AUG-2019