

PLEASANT TO USE



THE PRODUCT

Modern, attractive, flat styling characterises the COMTEC family of cases. This makes desktop units easy to operate, and applications on the wall – then rotated by 180° – can be optimally mounted for the user.

The new "Softline" design gives the cases a high-quality appearance for housing equipment that needs to look good.

YOUR ADVANTAGE

Ergonomic design. A real asset when operating and reading.


Large area for interfaces at the top. Ideal for D-sub-plug connectors, round connectors etc.

Flat or raised bottom part for large-volume components.

Protection class IP 40

Max. size of PCB (D x W in mm)

| | bottom part version I | top part |
|---------|--------------------------|-----------|
| 120 F | 94 x 123 | 105 x 137 |
| 120 H | 94 x 128 | 105 x 137 |
| 150 F/H | 124 x 175 | 130 x 187 |
| 200 F/H | 174 x 123 | 185 x 137 |
| 290 H | 264 x 167 | 270 x 187 |



detailed drawings see our website
www.okw.com



TABLE TOP OR WALL MOUNTED

Advantages for wall mounted applications

The ergonomically inclined front panel allows the case to be mounted within the operator's reach. Displays and readouts are easily legible for all users involved – be it the mechanical engineer, the operator etc.

Wall suspension element for rational wall mounting (accessory).

YOUR ADVANTAGE

Version I with closed bottom part. In version II the battery compartment can be fitted in the bottom parts (150 F/H, 200 F/H). Lid of battery compartment snapped-on.

Recessed operating area for the protection of the membrane keyboard.

Self-adhesive case feet ensure reliable desk-top positioning.

APPLICATIONS

Systems for data collection on the job and machines.

Communications equipment. Access and security controls and data systems engineering.



Medical field and laboratory technologies.

Measuring and controlling.

Industrial regulation.



COMTEC

| COMTEC | Outside dim. in mm | | | Version / Equipment (dim. in mm) | | Material | Part-No. | | | |
|--|--------------------|-----|---------|----------------------------------|-------------------|-------------------|-----------------------|-------------------|-------------|-------------|
| | W | D | H | battery compartment | max. dim. keypad | | off-white RAL 9002 | black RAL 9005 | | |
|  | 120 F | 120 | 150 | 20/42.8 | I | — | 87.85 x 109.85 | ABS (UL 94 HB) | A 06 12 007 | A 06 12 009 |
| | 120 H | 120 | 150 | 40/62.8 | I | — | 87.85 x 109.85 | ABS (UL 94 HB) | A 06 12 107 | A 06 12 109 |
| | 150 F | 150 | 200 | 20/51.5 | I | — | 117.85 x 159.80 | ABS (UL 94 HB) | A 06 15 007 | A 06 15 009 |
| | | 150 | 200 | 20/51.5 | II | • (see accessory) | 117.85 x 159.80 | ABS (UL 94 HB) | A 06 15 017 | A 06 15 019 |
|  | 150 H | 150 | 200 | 40/71.5 | I | — | 117.85 x 159.80 | ABS (UL 94 HB) | A 06 15 107 | A 06 15 109 |
| | | 150 | 200 | 40/71.5 | II | • (see accessory) | 117.85 x 159.80 | ABS (UL 94 HB) | A 06 15 117 | A 06 15 119 |
| | 200 F | 200 | 150 | 20/42.8 | I | — | 167.75 x 109.85 | ABS (UL 94 HB) | A 06 20 007 | A 06 20 009 |
| | | 200 | 150 | 20/42.8 | II | • (see accessory) | 167.75 x 109.85 | ABS (UL 94 HB) | A 06 20 017 | A 06 20 019 |
| 200 H | 200 | 150 | 40/62.8 | I | — | 167.75 x 109.85 | ABS (UL 94 HB) | A 06 20 107 | A 06 20 109 | |
| | 200 | 150 | 40/62.8 | II | • (see accessory) | 167.75 x 109.85 | ABS (UL 94 HB) | A 06 20 117 | A 06 20 119 | |
| | 290 H | 290 | 200 | 44/75.5 | I | — | 257.85 x 159.80 | ABS (UL 94 HB) | A 06 29 107 | A 06 29 109 |

COMTEC ACCESSORIES

| Article | For COMTEC | Version / Application | Part-No. |
|------------------------|------------------|--|-------------|
| ① Battery cradle kit | 150 F/H, 200 F/H | ABS, off-white, for 4 x 1.5 V mignon cells (AA), battery clips nickel-plated*1 | A 93 45 217 |
| ② Battery cradle | 150 F/H, 200 F/H | ABS, off-white, for 1 x 9 V flat battery (PP3) | A 91 74 003 |
| | 150 F/H, 200 F/H | ABS, off-white, for 2 x 9 V flat battery (PP3) | A 91 74 002 |
| ③ Set of battery clips | 150 F/H, 200 F/H | tin-plated, for 1 x 9 V flat battery (PP3) | A 91 74 006 |
| | 150 F/H, 200 F/H | tin-plated, for 2 x 9 V flat battery (PP3) | A 91 61 002 |
| ④ Plug-in contact | 150 F/H, 200 F/H | for 1 x 9 V flat battery (PP3) | A 91 60 003 |
| ⑤ Set of screws | all sizes | 4 x ø 2.5 x 6 mm, for mounting PCBs | A 91 99 008 |



universal accessories on pages 178-187

*1 complies with DIN EN 60601 (short circuit caused by incorrect insertion of batteries impossible)