

eccentric fitting tensioning clamps for fixture plates

without sliding block

Application:

Workpieces of any desired shape can be clamped with stop pins and one or two clamping screws.

Execution:

- eccentric screw 10.9 tempered
- hexagonal brass disc
- ref. no. 26222237 is a V2A hexagonal disc
- steel screw, brass or V2A stainless steel clamping washer

Advantage:

- quick and uncomplicated clamping
- compact size allows multiple workpieces to be clamped
- outstanding accessibility, perfect for 5-axis machining
- cost-effective clamping



Art. no.	26222 240
Brand	IBT
Manufacturer Part Number	X50210
Width across flats	20 mm
Thread dimension	M10
Hexagonal disc height	6.4 mm
Thread length	20 mm
Max. clamping width	1.6 mm
Material of clamping clip	Brass
Tension force	9 kN
Number of pieces in assortment/set	10 PCS
Gross Weight	0.281 kg
Product Group	278