

Forklift truck

Model GS EVO



Application:

For lifting and carrying loads on pallets or in standardised containers

Execution:

- For intensive use
- Compact design
- Chrome-plated piston rod and oil seal: Prevents rust formation and oil leaks during use
- Adjustable lowering speed: The lowering speed can be controlled in proportion to the lever position on the drawbar. Perfect for fragile and sensitive loads such as crystal, glass and ceramic
- Retracting and extending rollers: Facilitate entry into closed pallets
- 3D superior ergonomic control: Thanks to the two large grip side areas that ensure a perfect position, this version enables the user to enjoy an even better operating position with less force required compared to conventional handles
- Simple installation



Art. no.	50262 305
Brand	PRAMAC LIFTER
Fork roller diameter	82 mm
Manufacturer Part Number	TEBA1AVV100
Turning radius	2017 mm
Material	Steel
Load-carrying capacity	2500 kg
Fork length	1800 mm
Fork arm width	150 mm
Fork, external distance	525 mm
Min. lift height	85 mm
Lift height	200 mm
Fork castor design	Tandem
Castor-wheel diameter	200 mm
Material of steering wheels	Polyurethane
Steering wheel design	With aluminium inner core
With quick-lift function	No
With weighing system	No
Colour	Green Pantone 382
Surface	Powder-coated
Gross Weight	127.000 kg
Product Group	559

EAN

8018539089337