



**RCD/MCB, 32A, 30mA, miniature circuit-breaker trip curve C, 3pole+N,
residual current circuit-breaker trip characteristic: A**

EATON®
Powering Business Worldwide™

Part no. mRB4-32/3N/C/003-A
Article no. 167508
Catalog No. MRB4-32/3N/C/003-A

Design verification as per IEC/EN 61439

Technical data for design verification

Rated operational current for specified heat dissipation	I _n	A	32
Heat dissipation per pole, current-dependent	P _{vid}	W	0
Equipment heat dissipation, current-dependent	P _{vid}	W	12.8
Static heat dissipation, non-current-dependent	P _{vs}	W	0
Heat dissipation capacity	P _{diss}	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	40
			0

Technical data ETIM 6.0

Circuit breakers and fuses (EG000020) / Earth leakage circuit breaker (EC000905)

Electric engineering, automation, process control engineering / Electrical installation, device / Residual current protection system / MCB/RCCB combination (ecl@ss8.1-27-14-22-07 [AFZ810012])

Number of poles (total)		4
Number of protected poles		3
Nominal rated voltage	V	230
Nominal rated current	A	32
Rated fault current	A	0,03
Leakage current type		A
Current limiting class		3
Rated short-circuit breaking capacity EN 60898	kA	4
Rated short-circuit breaking capacity IEC 60947-2	kA	0
Frequency		50 Hz
Release characteristic		C
Concurrently switching N-neutral		Yes
Over voltage category		3
Pollution degree		2
Width in number of modular spacings		4
Built-in depth	mm	70
Suitable for flush-mounted installation		No
Degree of protection (IP)		IP20
Surge current capacity	kA	0.25
Voltage type		AC
Antinuisance tripping version		No