

ELECTROFLEX®

TECHNICALLY BLENDED SEAMLESS GLOVES WITH POLYURETHANE COATING



ISSUE No.1

PRODUCT DATASHEET

UPDATED 04/2015

CODE: TEF25HD

PRODUCT DESCRIPTION:

Cut level 4 seamless technically blended yarn glove with high-density clean polyurethane palm coating.

PRODUCT TYPE:

General handling with good cut and abrasion resistance

FEATURES AND BENEFITS:

HDPu – High density Polyurethane Coating
CPU – Clean Polyurethane Technology
Anti-bacterial agent
Maximum level 4 abrasion to EN388
Exceptional wet and dry grip properties
Strong durable Polyurethane palm coating
Excellent Dexterity

TYPICAL APPLICATIONS:

Glass / Automotive / Engineering / Utilities /
Component Assembly / Maintenance

SIZE: 6 / 7 / 8 / 9 / 10
Length: Average: 26cms

COLOUR:
Grey knitted shell with GREY PU coating.

PACKAGING:
12 Pairs per pack
120 Pairs per case



TECHNICAL DETAILS:

Tested in accordance with
EN 388, EC type examination
carried out by:

CTC, 4 Rue Hermann Frenkel,
69367 LYON
(Approved Body 0075)



The results are taken from the palm area of the glove and the uncoated surface may have reduced performance levels.

CERTIFICATE: 0075/057/162/09/14/0932



FOR MORE INFORMATION CONTACT

T: 0115 961 9555

f: 0115 961 9666

e: sales@tornadogloves.com

e: technical@tornadogloves.com

5B / Colwick Quays Business Park
Colwick Industrial Estate / Nottingham / NG4 2JY

www.tornadogloves.com

