

Twist drill type N HSS, steam-treated

for universal use up to 1000 N/mm²

ORION[®]

Application:

Standard geometry for universal use up to 1000 N/mm².

Execution:

- Twist drill with universal standard geometry

Advantage:

- excellent all-round properties and precise cutting pattern
- universal use: minimises tool costs and improves flexibility
- Steam treatment ensures favourable adherence of coolant



Art. no.	11071 267
Brand	ORION
Manufacturer Part Number	11071267
Cutting material	HSS
Surface	Vaporised
Type	N
Angle of the tip	118 Degree
DIN	345
Tool holding device	Morse taper shank
Cutting edge diameter	21.5 mm
Chip flute length	150 mm
Length	248 mm
Morse taper size	MK 2
f steel 700	0.32 mm/r
Gross Weight	0.400 kg
Product Group	1AP

EAN

4039247022878