

E-LITE LED Signal Light



RND 430-00120










RND 430-00121

Luce di segnalazione a led.

Led signal light.

Feu de signalisation à LED

CUPOLA <i>DOME</i> <i>DOME</i>	PC Opaline						
BASE <i>BASE</i> <i>BASE</i>	PC						
GUARNIZIONE <i>GASKET</i> <i>JOINT</i>	O-Ring EPDM						
CONNETTORE <i>CONNECTOR</i> <i>CONNECTEUR</i>	Cavo 2 poli <i>Cable 2 poles</i> <i>Câble 2 voies</i>						
GRUPPO OTTICO <i>LUMINOUS SOURCE</i> <i>SOURCE LUMINEUSE</i>	N°14 LED						
COLORI DISPONIBILI <i>AVAILABLE COLOURS</i> <i>COULEURS DISPONIBLES</i>	 						
VOLTAGGIO <i>VOLTAGE</i> <i>TENSION</i>	24 Vdc						
SERVIZIO <i>OPERATION</i> <i>FONCTIONNEMENT</i>	∞						
CORRENTE NOMINALE <i>CURRENT CONSUMPTION</i> <i>CONSUMMATION DE COURANT</i>	40 mA						
RESA LUMINOSA <i>LIGHT OUTPUT</i> <i>RENDEMENT LUMINEUX</i>	<table border="1"><tr><td>Cd (p)</td><td></td><td></td></tr><tr><td></td><td>12</td><td>5</td></tr></table>	Cd (p)				12	5
Cd (p)							
	12	5					
MODALITA' LUCE <i>LIGHT EFFECT</i> <i>EFFET LUMINEUX</i>	Fissa <i>Steady</i> <i>Fixe</i>						
GRADO IP <i>IP RATING</i> <i>DEGRE IP</i>	IP66						
GRADO IK <i>IK RATING</i> <i>DEGRE IK</i>	IK06						
TEMPERATURA DI FUNZIONAMENTO <i>OPERATING TEMPERATURE</i> <i>TEMPERATURE DE SERVICE</i>	-30°C+50°C						

E-LITE LED Signal Light



VIBRAZIONI

*VIBRATIONS
VIBRATIONS*

INDUSTRIAL CEI 60068-2-6 SINE

CERTIFICAZIONI, OMOLOGAZIONI

*CERTIFICATIONS, APPROVALS CERTIFICATIONS,
HOMOLOGATIONS*

CE, UKCA

FISSAGGIO

*MOUNTING
FIXATION*

Viti su base

*Screws on the base
Par vis sur la base*

DISEGNO

*TECHNICAL DRAWING
DESSIN*

