

General Information

Extended Product Type:	JB5-2
Product ID:	1SNK905302R0000
EAN:	3472599097551
Catalog Description:	JB5-2 Jumper Bar - Orange
Long Description:	Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking, - Perfectly adapted to low level electrical contact (20mA, 50mV).

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

Ordering

Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010
Color:	Orange

Dimensions

Product Net Height:	8.2 mm
Product Net Length:	26.8 mm
Product Net Depth:	26.8 mm
Product Net Weight:	1.3 g
Product Net Width:	5.2 mm

Technical

Spacing:	5.2 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 32 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 480 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	1 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	ZDK2.5-22 ZDP2.5-11 ZDP2.5-22 ZDP2.5-D1 ZDP2.5-D2 ZDS4-22 ZK2.5 ZK2.5-3P ZK2.5-4P ZK2.5-CH-4P ZK2.5-D1 ZK2.5-D1-PE ZK2.5-D2 ZK2.5-D2-PE ZK2.5-D-CH ZK2.5-PE ZK2.5-PE-3P ZK2.5-PE-4P ZK2.5-S ZK2.5-S-4P ZK2.5-SF ZK2.5-SF-R ZK2.5-SP ZK2.5-SP-4P ZK2.5-S-R1 ZP2.5 ZP2.5-3P ZP2.5-4P ZP2.5-D1

ZP2.5-D2
ZP2.5-PE
ZP2.5-PE-3P
ZP2.5-PE-4P
ZS4
ZS4-D1
ZS4-D2
ZS4-D2-S
ZS4-D2-S-T
ZS4-D-CH
ZS4-T3

Technical UL/CSA

Flammability According to UL94:	V0
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
ATEX Certificate:	1SND162004A1706
CB Certificate:	1SND161017A0202
Data Sheet, Technical Information:	1SNK160027D0201
RoHS Information:	1SND230499F0202

Classifications

E-nummer:	2925366
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block
Object Classification Code:	X

Container Information

Package Level 1 Width:	50 mm
Package Level 1 Length:	117 mm
Package Level 1 Height:	50 mm
Package Level 1 Gross Weight:	0.065 kg
Package Level 1 EAN:	3472599097551
Package Level 2 Units:	1500 piece
Package Level 3 Units:	144000 piece
Package Level 1 Units:	50 piece

