## **CA2005 Catering Thermometer**

#### T TYPE THERMOCOUPLE THERMOMETER WITH HOLD FUNCTION

#### **FEATURES**

Easy to use low cost high accuracy microprocessor based thermocouple instrument with the benefits of a hold function. This instrument has wide measurement range of -50 to +400 $^{\circ}$ C and an operating range of -30 to 50 $^{\circ}$ C.

\*\*\* Hold function with dual display

\*\*\* Preset to °C

\*\*\* Resolution of 0.1° to 1000° autoranging

\*\*\* Compatible with TME T type temperature probes

\*\*\* Auto Switch Off capability

\*\*\* Overrange / Open circuit sensor indication

\*\*\* Low battery indication

\*\*\* IP67 casing

## **SPECIFICATION**

## **Environmental**

AMBIENT OPERATING RANGE : -30 to 50 °C STORAGE TEMPERATURE RANGE : -40 to 50 °C HUMIDITY : 0 to 70% R.H.

#### **ELECTRICAL**

MEASUREMENT RANGES : -50 to +400°C

THERMOCOUPLE TYPES : T TEMPERATURE SCALES : °C

ACCURACY @23°C : +/- 0.1% OF READING +/- 0.2 °C

CHARACTERISING ACCURACY : LESS THAN 0.05 °C
TEMPERATURE COEFFICIENT : 0.01% OF READING /°C

COLD JUNCTION COMPENSATION : 0.0075 °C/°C

RESOLUTION : 0.1° to 1000, 1° ABOVE 1000

#### **GENERAL**

BATTERY : PP3 9V I.E.C. 6F22

BATTERY LIFE (INTERMITTENT USE) : GREATER THAN 200 HOURS (ALKALINE)

WEIGHT : 155 gms

DIMENSIONS : 130 X 70 X 33 mm

# Cross-reference for compatible probes

Suitable probes for use with this instrument

TME PART No	DESCRIPTION	APPLICATION	T/C TYPE
CAPK	SET OF 5 COLOUR CODED NEEDLE PROBES	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	Т
CAP-R	RED COLOUR CODED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	Т
CAP-B	BLUE COLOUR CODED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
CAP-G	GREEN COLOUR CODED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	Ť
CAP-W	WHITE COLOUR CODED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	Т
CAP-Y	YELLOW COLOUR CODED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	Т
TP05	NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	Т
TP07	NEEDLE PROBE HEAVY DUTY	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	Т
TP10	SOUS VIDE NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
-			
TM01	LIGHT DUTY M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	Т
TM03	M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	Т
TM04	M.I. PROBE EXTENDED LENGTH	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	Т
TS01-S	DUAL PROBE	FOR SURFACE AND IMMERSION MEASUREMENT	Т
TS04	SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	Т
TA04	AIR TEMPERATURE PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	Т
TA12	SPATULA PROBE	BETWEEN PACK PROBE	Т
TH01	SOCKET IN HANDLE	HANDLE FOR USE WITH PLUG MOUNTED PROBES	Т
THA2	PLUG MOUNTED AIR PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	Т
THM01	PLUG MOUNTED M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	Т
THN01	PLUG MOUNTED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	Т
THA12	PLUG MOUNTED NEEDLE PROBE	BETWEEN PACK PROBE	T
, (12	. 200 MODITED STATED AT HODE	DE TREET TORY TROPE	
THS02	PLUG MOUNTED SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	Т
PKF1	FOOD KIT	PROBE KIT DESIGNED FOR THE FOOD INDUTRY	Т
TP01	CORKSCREW PROBE	PROBE DESIGNED FOR CORE TEMPERATURE OF MEAT	Т
TFS01	FOOD SIMULANT PROBE	SIMULATES THE CORE TEMPERATURE OF FOOD IN HOT OR COLD STORAGE	