



## MEHRBEREICHSBLINDNIETE FLACHRUNDKOPF

## MULTIGRIP BLIND RIVETS DOMED HEAD


## RIVETS MULTI SERRAGE TÊTE PLATE









Aluminium AIMG 2,5  
Aluminium AIMG 2,5  
Aluminium AIMG 2,5


Stahl verzinkt  
Steel zinc plated  
Acier zingué







### Ø 4,8 mm

D1 = 4,8 + 0,05 / - 0,13 mm  
D2 = 9,5 + / - 0,29 mm  
k = ≤ 2,0 mm  
d = 2,78 mm  
P = ≥ 27,0 mm  
L = + 1,0 / - 0,2 mm  
 4,9 mm

	F-Max		CODE				
4,8 x 10,0 mm	14,5 mm	1,0 - 6,0 mm	77701 48100	1400 N	2000 N	500	5000
4,8 x 10,3 mm	14,8 mm	1,6 - 6,4 mm	77701 48103			500	5000
4,8 x 15,1 mm	19,6 mm	4,8 - 11,0 mm	77701 48150			500	5000
4,8 x 17,0 mm	21,5 mm	6,4 - 12,7 mm	77701 48170			500	5000
4,8 x 18,0 mm	22,5 mm	8,0 - 14,0 mm	77701 48180			500	5000
4,8 x 20,0 mm	24,5 mm	10,0 - 16,0 mm	77701 48200			500	5000
4,8 x 24,8 mm	29,3 mm	12,7 - 21,0 mm	77701 48248			500	5000
4,8 x 30,0 mm	34,5 mm	20,0 - 25,0 mm	77701 48300			250	2500

### Ø 6,4 mm

D1 = 6,4 + 0,08 / - 0,15 mm  
D2 = 13,0 + / - 0,3 mm  
k = 2,0 + 0 / - 0,3 mm  
d = 3,65 mm  
P = ≥ 32,0 mm  
L = + 1,0 / - 0,2 mm  
 6,5 mm

	F-Max		CODE				
6,4 x 15,0 mm	21,4 mm	1,5 - 9,0 mm	78801 64150	2600 N	3800 N	250	2500
6,4 x 20,0 mm	26,4 mm	6,0 - 14,0 mm	78801 64200			250	2500
6,4 x 25,0 mm	31,4 mm	10,0 - 18,0 mm	78801 64250			250	2500