

Coaxial Cable Connector 24_TNC-50-2-1/133_N

Description

Straight bulkhead cable feed through

Interface standards

IEC 60169-17_MIL-STD-348A/313_CECC 22200



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 11 GHz

Mechanical Data

Centre contact soldered
Outer 2contact clamped
Weight 0.0209 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	
Washer	Bronze	

Related Documents

Outline drawing DOU-00009424
Catalogue drawing DCA-00009240
Assembly instruction DOC-0000179064
Mounting hole DOU-00008751

Ordering Information

Single package 24_TNC-50-2-1/133_NE

Additional Information

Suitable cables RG_316_/U, RG_188_A/U, RG_174_/U