

Column-mounted slewing jib crane ASSISTENT AS – complete set with compound anchor system and chain hoist

Lives up to its name



Application:

Perfect for halls/rooms with low ceilings.

Execution:

- classification according to EN 13001 HC2 S2 HD2 for light industrial use
- power supply with round trailing cable
- lockable isolating switch
- Operating voltage: 400 V/50 Hz, control voltage: 24 V
- Electric chain hoist with manual sliding chassis – two-stage lifting speed
- Swivel range 270°
- **WITH DÜBEL MOUNTING SYSTEM VAS2 (simple installation and no foundation required)**

Advantage:

- Solid construction
- Ideal for halls/rooms with low ceilings
- Cost-effective to assemble and rapid to commission thanks to a compound anchor system (no foundation or bottom casting)

Delivery:

Incl. detailed documentation



Art. no.	77111 023
Brand	VETTER
Manufacturer Part Number	AS2,5-3,0+VAS2+SIXX2F-
Load-carrying capacity	250 kg
Overhang	3000 mm
Construction height	2790 mm
Model	ASSISTENT AS
Lower edge of crane bottom	2500 mm
Max. lift height	2067 mm
Lifting device design	With electric chain hoist SIXX-HF
Mounting plate diameter	530 mm
Design	With electric chain hoist and VAS2
Height of hoist	433 mm
Stroke speed of precision hoist	1.5 m/min
Stroke speed of main hoist	6 m/min
Flange width	91 mm
Surface	Lacquered
Weight	259 kg
Operating voltage	400 V
Swivel range	270 Degree
Colour	Daffodil yellow RAL 1007
Max. vertical force	1115 kN
Product category	B2B produkt
Gross weight	335 kg
Made in	Germany
Gross Weight	335.000 kg
Product Group	7EL