
	DATA SHEET	2170476
	ETHERLINE® H PiMF * * 4 x 2 x AWG22/1 CAT.7	Valid from: 02.12.2008

Industrial Ethernet CAT. 7

* * UL/CSA Approval in preparation



Application:

High speed cable for Industrial Ethernet for fixed installations in dry, wet or damp rooms. Cable meets the transmission characteristics for Category 7 of IEC 61156-5 Ed. 2. Beyond the outstanding electrical properties the halogenfree design enables these cables especially for applications wherever people, machinery and equipment are endangered by fire or smoke emission.

Design

Solid bare copper wire \varnothing 0,64 (AWG22/1)	\varnothing 0.64 mm (0.025 in)
Insulation of foamed Polyethylene (PE) with skin	\varnothing 1.52 mm (0.059 in) nom.
	\varnothing 1.60 mm (0.063 in) max.

Core

2 cores individually screened with aluminium bonded plastic tape and stranded to form the stranded element

Sequence of colours: pair 1: white / blue (WH/BU)-blue (BU),
pair 2: white / orange (WH/OG)-orange (OG)
pair 3: white / green (WH/GN)-green (GN),
pair 4: white / brown (WH/BN)-brown (BN)

Shield braiding of tinned copper wires 0.13 mm diameter (36 AWG)

Coverage approx. 85%

Non woven tape, longitudinally applied	\varnothing 6.7 mm (0.264 in)
--	---------------------------------

Jacket

Special halogen free compound, green (GN)


Wall thickness approx. 1.0 mm

\varnothing 8.7 \pm 0.3 mm (0.343 \pm 0.012 in)
--

LAPP KABEL STUTT GART **ETHERLINE® H PiMF CAT. 7**

4 x 2 x AWG22/1 SHIELDED ROHS ART. 2170476

prepared by: PD-AN Hans Euler	Document: DB2170476EN	Page 1 of 2
----------------------------------	-----------------------	-------------



DATA SHEET

2170476

ETHERLINE® H PiMF * *
4 x 2 x AWG22/1 CAT.7

Valid from:
02.12.2008

Electrical data at 20°C

Loop resistance	≤ 118,2 Ohm/km
Signal run time	≤ 4.7 ns/m
Insulation resistance	≥ 5 GOhm*km
Capacitance at 800 Hz	approx. 45 pF/m
Velocity of propagation	nom. 79%
Characteristic impedance:	
1 - 100 MHz	100 (±15) Ohm
100 - 500 MHz	100 (± 22) Ohm
Operating voltage (peak)	≤ 100V
Test voltage (wire/wire/screen rms 50Hz 1min)	700V

Frequency (MHz)	4	10	16	20	31.25	62.5	100
NEXT (dB) ≥	78	78	78	78	78	75.5	72.4
Attenuation max. (dB/100m) (dB/100ft)	3.7 (1,13)	5.9 (1.80)	7.4 (2.26)	8.3 (2.53)	10.4 (3.17)	14.9 (4.54)	19.0 (5.79)

Frequency (MHz)	155	200	250	300	500	600
NEXT (dB) ≥	69.5	67.9	66.4	65.2	61.9	60.7
Attenuation max. (dB/100m) (dB/100ft)	24.0 (7.32)	27.5 (8.35)	31.0 (9.5)	34.2 (10.4)	45.3 (13.8)	50.1 (15.3)

Other electrical requirements acc. to IEC 61156-5 Ed. 2

Mechanical and thermal characteristics

- Conductor material acc. to DIN EN 13602 Cu-ETP-R460-P
- Screen material acc. to DIN EN 13602 Cu-ETP-A013-C
- Insulating material acc. to DIN EN 50290-2-23 (VDE 0819), table 2/B
- Jacket material acc. to VDE 0207, compound type HM2
- Flame retardant acc. to IEC 60332-3
- Stripping of sheath: min. 5 N to max. 40 N at a length of 50 mm

Other characteristics:

RoHS compliant

Permissible temperature range:	-25 °C (-13 °F) up to 80 °C (176 °F)
Min. bending radius allowed:	single 10 x Ø
Weight approx.:	99 kg/km (67 lb/1000 ft)

prepared by:
PD-AN Hans Euler

Document: DB2170476EN

Page 2 of 2