

Flat-bed hand truck with wire grid walls

with drawbar eye

fetra
Transportgeräte

Execution:

- Modular system
- From welded profile steel, 4 tubular sleeves at corners
- Scissors-shaped drawbar with safety handle with soft rubber grip and with an automatic damped retraction in resting position
- Load area covered with slip-resistant phenolic resin coated waterproof plywood
- Board walls 600 mm high, front walls screwed with platform, longitudinal walls can be hooked in and removed
- Board walls made of steel tube frames
- with welded-in
- wire grid 40 x 40 x 4 mm
- Load area =
- Length - 65 mm,
- Width - 5 mm.
- Automatic locking brake acting on the front wheels, according to EN 1757-3
- with drawbar eye
- Powder coating: RAL 5007, brilliant blue, durable surface protection, impact and scratch-resistant



Art. no.	50267 883
Brand	FETRA
Manufacturer Part Number	6434LZ
Length	1550 mm
Height	1200 mm
Loading surface length	1200 mm
Width	850 mm
Loading-surface width	800 mm
Loading surface size	1200 x 800 mm
Loading-surface height	490 mm
Load-carrying capacity	1000 kg
Total stop optional	No
Wheel width	100 mm
Wheel diameter	400 mm
Material of wheel	Air
Gross Weight	99.000 kg
Product Group	5AE

EAN

4017976434032