
IEC Appliance Outlet F or H, Screw-on Mounting, Front Side, Solder or Quick-connect Terminal





Description

- Panel mount :
- Screw-on mounting , from front side
- 1 Function :
- Connector , Pin temperature 70 °C , protection class I or II
- Solder/Quick Connect Terminal

Technical Data

iechnical Data				
Ratings IEC	10A / 250VAC; 50Hz	Appliance inlet/-outlet	F acc. to IEC 60320-3 /	
Ratings UL/CSA	15 A / 250 VAC; 60 Hz		H UL 498, CSA C22.2 no. 42 (for cold	
Dielectric Strength	> 4 kVAC between L-N > 2 kVAC between L/N-PE (1 min/50 Hz)		conditions) pin-temperature 70 °C, 10 Protection Class I or II	
Allowable Operation Tempe- rature	-25 °C to 70 °C			
IP-Protection	from front side IP20 acc. to IEC 60529			
Protection against electric shock	Suitable for appliances with protection class I or II acc. to IEC 61140			
Terminal	Solder/Quick Connect Terminal			
Material: Housing	PA6, black or grey, UL 94V-0			

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: 5098

Approval Logo	Certificates	Certification Body	Description
	VDE Approvals	VDE	VDE Certificate Number: 40010295
AI	UL Approvals	UL	UL File Number: E57445
c ^{CD} us	CSA Approvals	CSA	CSA Certification Record: 27324

See below: Approvals and Compliances

References

We recommend for new applications the type 6600-3

Weblinks

pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Accessories, Detailed request for product

Product standards

Product standards that are referenced

Design	Standard	Description
Designed according to	IEC 60320-1	Appliance couplers for household and similar general purposes
Designed according to	IEC 60320-3	Appliance couplers for household and similar general purposes
Designed according to	UL 498	Standard for Attachment Plugs and Receptacles
Designed according to	CSA C22.2 no. 42	General Use Receptacles, Attachment Plugs, and Similar Wiring Devices
	Designed according to Designed according to Designed according to	Designed according toIEC 60320-1Designed according toIEC 60320-3Designed according toUL 498

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
IEC	Designed for applications acc.	IEC/UL 62368-1	IEC 62368-1 includes the basic requirements for safety of audio, video, information technology and office equipment.

Compliances


The product complies with following Guide Lines

	-		
Identification	Details	Initiator	Description
CE	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
ROHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
(China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

40

32.4-0+0.2

Dimensions [mm]



Length of the terminal please find at the order code configuration table

Config. Code

5098 - H - A B C 0- D - E

The characters are placeholders for the correspondingly keys of selections from the key tables.

5098 - H - A B C 0- D - E = Type		Туре	Configuration key
Туре	Configuration key	protection class I	X
protection class II	В		
		5098 - H - A B C 0- D - E = Terminals	

Terminal L		Configuration key
solder terminal		1
PCB-terminal standard		4
Blade terminal (6.3 x 0.8 mm)	0	9

5098	- H	- A	BC	0-	D -	Ε =	= Terminals
------	-----	-----	----	----	-----	-----	-------------

Terminal N	Configuration key
solder terminal	1
PCB-terminal standard	4
Blade terminal (6.3 x 0.8 mm)	9
Symbols similar as in table A	

5098	- H - A	в С 0-	D - E	= Terminals
------	---------	--------	-------	-------------

Terminal GroundConfiguration
keywithout terminal0solder terminal1PCB-terminal standard4Blade terminal (6.3 x 0.8 mm)9Symbols similar as in table A

5098 - H - A B C 0- **D** - E **= Color**

Color	Configuration key
Black	А
Grey	В

5098 - H - A B C 0- D - **E** = Style

Style	Configuration key
flange with countersunk holes	1
flange with through holes	2

All Variants

Туре	Terminals L / N	Terminal Ground	Color	Style	Features	Config. Code	Order Number	
Protection class II	Blade terminal (6.3 x 0.8 mm)		black	Flange with countersunk holes	-	5098-B-9900-A-1	6182.0027	
Protection class I	solder terminal	solder terminal	black	Flange with countersunk holes	-	5098-X-1110-A-1	6182.0028	
Protection class I	solder terminal	solder terminal	grey	Flange with countersunk holes	-	5098-X-1110-B-1	6182.0030	
Protection class I	Blade terminal (6.3 x 0.8 mm)	Blade terminal (6.3 x 0.8 mm)	black	Flange with countersunk holes	-	5098-X-9990-A-1	6182.0031	
Protection class I	Blade terminal (6.3 x 0.8 mm)	Blade terminal (6.3 x 0.8 mm)	grey	Flange with countersunk holes	-	5098-X-9990-B-1	6182.0032	

The listed variants should be available from stock. Other versions on request www.schurter.com/contact

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Packaging unit 50 Pcs

Accessories

Description



RC320 Rear Cover for Power Entry Module

Mating Inlets/Plugs

Category / Description

Plug Overview complete



4732, Mounting: Power Cord, Plug: IEC E, Cable	4732
4735, Mounting: Power Cord, Plug: IEC E, Cable	4735
9009, Mounting: Plug: IEC E, Screw clamps	9009
4733, Mounting: Power Cord, Plug: IEC E, Cable	4733
4736, Mounting: Power Cord, Plug: IEC E, Cable	4736