


KEMET Part Number: T491D226K016ZT
(B45196E3226K409)

Capacitor, tantalum, 22 uF, 7343, +/-10% Tol, 16V@85C



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.3	+/-0.3
W	4.3	+/-0.3
H	2.8	+/-0.3
K	1.8	typ
F	2.4	+/-0.1
S	1.3	+/-0.3

Notes:

-In polarity stripe, at KEMET's option, type may be indicated: see catalog for explanation of symbols

-Old part number [Obsolete] was B45196E3226K409

General Information

Manufacturer:	KEMET
Construction:	Standard Chip-MnO2

Specifications

Capacitance:	22 uF
Voltage DC @ 85C:	16V
Voltage DC @ 105C:	13V
Voltage DC @ 125C:	10V
Tolerance:	+/-10%
Application:	General Purpose
Temperature Range:	-55/+125C
Body Type:	Molded Chip
Footprint:	7343
Termination:	Tin
RoHS:	Yes
Leakage Current:	3.6 uA
Dissipation Factor:	6%
Impedance @ 100kHz:	1.1 Ohm

Packaging Specifications

Package Kind:	T&R
Package Size:	7in
Package Quantity:	750