

# Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number :

7447779147

LF




Bezeichnung : **SPEICHERDROSSEL WE-PD**

description : **POWER-CHOKE WE-PD**

DATUM / DATE : 2004-10-11

## A Mechanische Abmessungen / dimensions :



● = Start of winding


Marking = Inductance code

|   | Typ M     |    |
|---|-----------|----|
| A | 7,3 ± 0,3 | mm |
| B | 4,5 ± 0,3 | mm |
| C | 1,5 ± 0,2 | mm |
| D | 1,5 ± 0,3 | mm |
| E | 4,0 ± 0,3 | mm |
|   |           |    |
|   |           |    |
|   |           |    |

## B Elektrische Eigenschaften / electrical properties :

| Eigenschaften / properties               | Testbedingungen / test conditions |                     | Wert / value | Einheit / unit | tol. |
|------------------------------------------|-----------------------------------|---------------------|--------------|----------------|------|
| Induktivität / inductance                | 1 kHz / 0,25V                     | L                   | 47,0         | μH             | ±20% |
| DC-Widerstand / DC-resistance            | @ 20 °C                           | R <sub>DC typ</sub> | 0,190        | Ω              | typ. |
| DC-Widerstand / DC-resistance            | @ 20 °C                           | R <sub>DC max</sub> | 0,260        | Ω              | max. |
| Nennstrom / rated current                | ΔT= 40 K                          | I <sub>DC</sub>     | 1,03         | A              | max. |
| Sättigungsstrom / saturation current     | ΔL/L  < 10%                       | I <sub>sat</sub>    | 1,10         | A              | typ. |
| Eigenres.-Frequenz / self-res.-frequency |                                   | SRF                 | 10,0         | MHz            | typ. |

## C Lötpad / soldering spec. :



## D Prüfgeräte / test equipment :

HP 4274 A für/for L und/and Q

HP 34401 A für/for I<sub>DC</sub> und/and R<sub>DC</sub>

## E Testbedingungen / test conditions :

Luftfeuchtigkeit / humidity: 33%  
Umgebungstemperatur / temperature: +20 °C

## F Werkstoffe & Zulassungen / material & approvals :

Basismaterial / base material: Ferrit/ferrite  
Endoberfläche / finishing electrode: 100% Sn  
Anbindung an Elektrode / soldering wire to plating: Sn/Ag/Cu - 96.5/3.0/0.5%  
Draht / wire: 2SFBW; 155°

## G Eigenschaften / general specifications :

Betriebstemp. / operating temperature: -40 °C - + 125 °C  
Umgebungstemp. / ambient temperature: -40 °C - + 85 °C  
It is recommended that the temperature of the part does not exceed 125 °C under worst case operating conditions.

Freigabe erteilt / general release:

Kunde / customer

|      |                         |              |
|------|-------------------------|--------------|
| MST  | Version 8               | 04-10-11     |
| SST  | Version 7               | 04-07-28     |
| SST  | Version 6               | 04-04-21     |
| SST  | Version 5               | 04-04-15     |
| MST  | Version 4               | 03-12-10     |
| AG   | Version 3               | 02-11-05     |
| AG   | Version 2               | 02-05-14     |
| JH   | Version 1               | 00-12-06     |
| Name | Änderung / modification | Datum / date |

Datum / date

Unterschrift / signature

Würth Elektronik

Geprüft / checked

Kontrolliert / approved

**Würth Elektronik eiSos GmbH & Co. KG**

D-74638 Waldenburg · Max-Eyth-Straße 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400  
http://www.we-online.com

# Spezifikation für Freigabe / specification for release


Kunde / customer : \_\_\_\_\_  
 Artikelnummer / part number : **7447779147**  
 Bezeichnung : **SPEICHERDROSSEL WE-PD**  
 description : **POWER-CHOKE WE-PD**

LF



DATUM / DATE : 2004-10-11

## H Induktivitätskurve / Inductance curve :



|                                     |                          |      |                         |              |
|-------------------------------------|--------------------------|------|-------------------------|--------------|
| Freigabe erteilt / general release: | <b>Kunde / customer</b>  | MST  | Version 8               | 04-10-11     |
|                                     |                          | SST  | Version 7               | 04-07-28     |
|                                     |                          | SST  | Version 6               | 04-04-21     |
|                                     |                          | SST  | Version 5               | 04-04-15     |
| .....                               | .....                    | MST  | Version 4               | 03-12-10     |
| Datum / date                        | Unterschrift / signature | AG   | Version 3               | 02-11-05     |
| .....                               | <b>Würth Elektronik</b>  | AG   | Version 2               | 02-05-14     |
|                                     |                          | JH   | Version 1               | 00-12-06     |
|                                     |                          | Name | Änderung / modification | Datum / date |
| Geprüft / checked                   | Kontrolliert / approved  |      |                         |              |

### Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Straße 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400  
<http://www.we-online.com>

# Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number :

7447779147

LF




Bezeichnung : **SPEICHERDROSSEL WE-PD**

description : **POWER-CHOKE WE-PD**


DATUM / DATE : 2004-10-11

## I Rollenspezifikation / tape and reel specification :




### Gurtspezifikation / Tape specification:

|   |                     |    |
|---|---------------------|----|
| A | 10,0 ± 0,1          | mm |
| B | 16,0 ± 0,2          | mm |
| C | 1,50 ± 0,1<br>- 0,0 | mm |
| D | 4,00 ± 0,1          | mm |
| E | 2,00 ± 0,1          | mm |
| F | 1,75 ± 0,1          | mm |
| G | 10,0 ± 0,1          | mm |
| H | 5,00 ± 0,1          | mm |



### Rollenspezifikation / Reel specification:

|   |             |    |
|---|-------------|----|
| a | 330,0 ± 2,0 | mm |
| b | 21,00 ± 0,8 | mm |
| c | 13,00 ± 0,5 | mm |
| d | 100,0 ± 1,0 | mm |



The force for tearing off cover tape is  
10 to 130 grams in arrow direction

Freigabe erteilt / general release:

Kunde / customer

MST

Version 8

04-10-11

SST

Version 7

04-07-28

SST

Version 6

04-04-21

SST

Version 5

04-04-15

MST

Version 4

03-12-10

AG

Version 3

02-11-05

AG

Version 2

02-05-14

JH

Version 1

00-12-06

Name

Änderung / modification

Datum / date

Datum / date

Unterschrift / signature

Würth Elektronik

Geprüft / checked

Kontrolliert / approved

This electronic component has been designed and developed for usage in general electronic equipment. Before incorporating this component into any equipment where higher safety and reliability is especially required or if there is the possibility of direct damage or injury to human body, for example in the range of aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc, Würth Elektronik eiSos GmbH must be informed before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

**Würth Elektronik eiSos GmbH & Co. KG**

D-74638 Waldenburg · Max-Eyth-Straße 1 · 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400

<http://www.we-online.com>