

SAFETY DATA SHEET

Swarfega Duck Oil

According to Regulation (EC) No 1907/2006, Annex II, as amended.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Swarfega Duck Oil

Product number 7118537, CNT84PSP, SDO25L, SDO5L, D869KL

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Lubricant. Car maintenance product. Releasing agent. For full details regarding recommended uses please refer to the product label.

1.3. Details of the supplier of the safety data sheet

Supplier SC Johnson Professional Ltd
 Denby Hall Way
 Denby
 Derbyshire
 DE5 8JZ
 +44 (0) 1773 855100
 info.prouk@scj.com

1.4. Emergency telephone number

Emergency telephone National Poisons Information Service (UK) 0344 8920111 (Health Professionals only)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Not Classified

Health hazards Asp. Tox. 1 - H304

Environmental hazards Not Classified

2.2. Label elements

Hazard pictograms



Signal word Danger

Hazard statements H304 May be fatal if swallowed and enters airways.

Precautionary statements P301+P310 IF SWALLOWED: Immediately call a POISON CENTER/ doctor.
 P331 Do NOT induce vomiting.
 P405 Store locked up.
 P501 Dispose of contents/ container in accordance with national regulations.
 P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Swarfega Duck Oil

Contains	DISTILLATES PETROLEUM HYDROCARBON LIGHT
Detergent labelling	≥ 30% aliphatic hydrocarbons, 5 - < 15% non-ionic surfactants

2.3. Other hazards

This substance is not classified as PBT or vPvB according to current EU criteria.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics	60-100%
CAS number: 64742-47-8	EC number: 926-141-6
	REACH registration number: 01-2119456620-43-XXXX
Classification	
Asp. Tox. 1 - H304	
ISO-BUTANOL	<1%
CAS number: 78-83-1	EC number: 201-148-0
	REACH registration number: 01-2119484609-23-0000
Classification	
Flam. Liq. 3 - H226	
Skin Irrit. 2 - H315	
Eye Dam. 1 - H318	
STOT SE 3 - H335, H336	

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	Remove affected person from source of contamination. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Get medical attention if any discomfort continues.
Ingestion	Never give anything by mouth to an unconscious person. Do not induce vomiting. Do not induce vomiting. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Get medical attention immediately.
Skin contact	Remove contaminated clothing. Wash skin thoroughly with soap and water. Get medical attention promptly if symptoms occur after washing.
Eye contact	Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes and get medical attention.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	Nausea, vomiting. Vapours may cause drowsiness and dizziness. Upper respiratory irritation.
Ingestion	Diarrhoea. Nausea, vomiting. Fumes from the stomach contents may be inhaled, resulting in the same symptoms as inhalation.
Skin contact	Prolonged contact may cause redness, irritation and dry skin.

Swarfega Duck Oil

Eye contact Irritating to eyes. Symptoms following overexposure may include the following: Redness. Pain.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor No specific recommendations.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media Extinguish with foam, carbon dioxide, dry powder or water fog.

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products Oxides of carbon.

5.3. Advice for firefighters

Protective actions during firefighting No specific firefighting precautions known.

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Environmental precautions Do not discharge into drains or watercourses or onto the ground.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Wear suitable protective equipment, including gloves, goggles/face shield, respirator, boots, clothing or apron, as appropriate. Absorb in vermiculite, dry sand or earth and place into containers. Avoid the spillage or runoff entering drains, sewers or watercourses.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Avoid spilling. Provide adequate ventilation.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store in a closed container. Store in a cool and well-ventilated place.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

ISO-BUTANOL

Swarfega Duck Oil

Long-term exposure limit (8-hour TWA): WEL 50 ppm 154 mg/m³

Short-term exposure limit (15-minute): WEL 75 ppm 231 mg/m³

WEL = Workplace Exposure Limit.

Distillates (petroleum), hydrotreated heavy paraffinic (CAS: 64741-88-4)

DNEL

Workers - Inhalation; Long term local effects: 5.4 mg/m³

Consumer - Inhalation; Long term local effects: 1.2 mg/m³

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

This product must not be handled in a confined space without adequate ventilation.

Eye/face protection

The following protection should be worn: Wear tight-fitting, chemical splash goggles or face shield. Personal protective equipment for eye and face protection should comply with European Standard EN166.

Hand protection

The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. Wear protective gloves made of the following material: Nitrile rubber. Polyvinyl alcohol (PVA). Viton rubber (fluoro rubber).

Other skin and body protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

Hygiene measures

Wash promptly with soap and water if skin becomes contaminated. Wash at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke.

Respiratory protection

No specific recommendations. Respiratory protection may be required if excessive airborne contamination occurs.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid.
Colour	Brown.
Odour	Characteristic.
Odour threshold	Not determined.
pH	Scientifically unjustified.
Melting point	Not determined.
Initial boiling point and range	Not determined.
Flash point	70 deg C°
Evaporation rate	Not determined.
Upper/lower flammability or explosive limits	Not determined.

Swarfega Duck Oil

Vapour pressure	Not determined.
Vapour density	Not determined.
Relative density	Not determined.
Solubility(ies)	Insoluble in water.
Partition coefficient	Not determined.
Auto-ignition temperature	Not determined.
Decomposition Temperature	Not determined.
Viscosity	Not determined.
Explosive properties	Not determined.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

Other information	No information required.
--------------------------	--------------------------

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	There are no known reactivity hazards associated with this product.
-------------------	---

10.2. Chemical stability

Stability	Stable at normal ambient temperatures.
------------------	--

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	Not relevant.
---	---------------

10.4. Conditions to avoid

Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
----------------------------	---

10.5. Incompatible materials

Materials to avoid	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
---------------------------	--

10.6. Hazardous decomposition products

Hazardous decomposition products	Does not decompose when used and stored as recommended.
---	---

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀)	Based on available data the classification criteria are not met.
-------------------------------------	--

Acute toxicity - dermal

Notes (dermal LD₅₀)	Based on available data the classification criteria are not met.
---------------------------------------	--

Acute toxicity - inhalation

Notes (inhalation LC₅₀)	Based on available data the classification criteria are not met.
---	--

Skin corrosion/irritation

Animal data	Based on available data the classification criteria are not met.
--------------------	--

Swarfega Duck Oil

Serious eye damage/irritation

Serious eye damage/irritation Based on available data the classification criteria are not met.

Respiratory sensitisation

Respiratory sensitisation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vivo Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Does not contain any substances known to be carcinogenic.

Reproductive toxicity

Reproductive toxicity - development Does not contain any substances known to be toxic to reproduction.

Specific target organ toxicity - single exposure

STOT - single exposure Based on available data the classification criteria are not met.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Based on available data the classification criteria are not met.

Inhalation Prolonged inhalation of high concentrations may damage respiratory system.

Ingestion Harmful: may cause lung damage if swallowed. Nausea, vomiting. Diarrhoea.

Skin contact Prolonged contact may cause dryness of the skin.

Eye contact May cause temporary eye irritation.

Toxicological information on ingredients.

Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics

Acute toxicity - oral

Acute toxicity oral (LD₅₀) 5,000.0
mg/kg)

Acute toxicity - dermal

Acute toxicity dermal (LD₅₀) 5,000.0
mg/kg)

Acute toxicity - inhalation

Notes (inhalation LC₅₀) LC50 (8h) >5000mg/m3 rat OECD 403

Skin corrosion/irritation

Animal data Erythema/eschar score: Well defined erythema (2). Oedema score: Very slight oedema - barely perceptible (1).

Serious eye damage/irritation

Serious eye damage/irritation Based on available data the classification criteria are not met.

Respiratory sensitisation

Respiratory sensitisation Guinea pig: Not sensitising.

Swarfega Duck Oil

Skin sensitisation

Skin sensitisation Guinea pig maximization test (GPMT) - Guinea pig: Not sensitising. Repeated exposure may cause skin dryness or cracking.

Germ cell mutagenicity

Genotoxicity - in vitro Genome mutation: Negative.

Genotoxicity - in vivo Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity NOAEC \geq 2200/1100 mg/m³, ,

Reproductive toxicity

Reproductive toxicity - fertility - NOAEL 750 mg/kg/day, Oral, Rat F1

Reproductive toxicity - development - NOAEL: \geq 5220 mg/m³, Inhalation, Rat

Specific target organ toxicity - single exposure

STOT - single exposure Based on available data the classification criteria are not met.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Based on available data the classification criteria are not met.

Aspiration hazard

Aspiration hazard May be fatal if swallowed and enters airways.

SECTION 12: Ecological information

Ecotoxicity Not regarded as dangerous for the environment.

12.1. Toxicity

Toxicity The product is not expected to be hazardous to the environment.

Acute aquatic toxicity

Acute toxicity - terrestrial Not known.

Ecological information on ingredients.

Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics

Acute aquatic toxicity

Acute toxicity - fish LC₅₀, 96 hours: >1000 mg/l, Fish

Acute toxicity - aquatic invertebrates EC₅₀, 48 hours: >1000 mg/l, Daphnia magna

Acute toxicity - aquatic plants IC₅₀, 72 hours: >1000 mg/l, Algae

Acute toxicity - microorganisms EL50, 48 hour: >10000 mg/l,

Chronic aquatic toxicity

Chronic toxicity - aquatic invertebrates , 21 days: 1.22 mg/l, Daphnia magna

12.2. Persistence and degradability

Swarfega Duck Oil

Persistence and degradability There are no data on the degradability of this product.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient Not determined.

12.4. Mobility in soil

Mobility The product is insoluble in water and will spread on the water surface.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This substance is not classified as PBT or vPvB according to current EU criteria.

12.6. Other adverse effects

Other adverse effects None known.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information Waste is classified as hazardous waste. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. Avoid the spillage or runoff entering drains, sewers or watercourses.

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

Road transport notes Not classified.

Rail transport notes Not classified.

Sea transport notes Not classified.

Air transport notes Not classified.

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

Not applicable.

Transport labels

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

Swarfega Duck Oil

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78
and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation

Dangerous Substances Directive 67/548/EEC.
 Dangerous Preparations Directive 1999/45/EC.
 Commission Directive 91/322/EEC of 29 May 1991 on establishing indicative limit values by implementing Council Directive 80/1107/EEC on the protection of workers from the risks related to exposure to chemical, physical and biological agents at work.
 Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).
 Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).
 Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work (as amended).
 System of specific information relating to Dangerous Preparations. 2001/58/EC.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

General information

Only trained personnel should use this material.

Key literature references and sources for data

Where Exposure Scenarios for the substances listed in Section 3 are available they have been assessed for the uses identified in this data sheet or on the product label and the appropriate relevant information is incorporated into this Safety Data Sheet.

Revision comments

SDS amended in line with REGULATION (EC) No 1272/2008 on Classification, Labelling and Packaging of Substances and Mixtures (as amended)

Revision date

15/08/2019

Revision

9

Supersedes date

29/07/2019

Hazard statements in full

H226 Flammable liquid and vapour.
 H304 May be fatal if swallowed and enters airways.
 H315 Causes skin irritation.
 H318 Causes serious eye damage.
 H335 May cause respiratory irritation.
 H336 May cause drowsiness or dizziness.

Notes for Hazard Statements in Full

The full text for Hazard Statements in section 16 relates to the reference numbers in sections 2 and 3 and not necessarily the finished product classification.

Swarfega Duck Oil

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.